




	T40622X4003-00X	T40622X4004-00X
VIEW A	PIN4 BLACK PIN1 BROWN PIN3 BLUE	PIN2 WHITE PIN4 BLACK PIN1 BROWN PIN3 BLUE
VIEW B	PIN4 BLACK PIN3 BLUE PIN1 BROWN	PIN4 BLACK PIN2 WHITE PIN3 BLUE PIN1 BROWN

TECHNICAL DATA	T40622X4003-00X	T40622X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

-	-	TE LABLE	14
	STEEL	WAVE WASHER	13
	STEEL	SPRING	12
	BRASS	SHIELDING	11
-	-	CABLE	10
-	COPPER ALLOY	COUPLING NUT	9
	RUBBER	O-RING	8
BALCK COLOR	PA66	HOUSING	7
GOLD FLASH	COPPER ALLOY	CONTACT	6
	COPPER ALOY	SHIELDING	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm ² (24AWG)	STANDARD: -001:0.5M -002:1.0M -003:1.5M -004:3.0M -005:5.0M -006:7.0M -007:10.0M CUSTOMIZATION: -XX0:XX.0 M -XX5:XX.5 M -99X: 0.X M	FIXED: -25°C~80°C FLXIBLE: -10°C~80°C	GRAY	PUR (UL)	RPC-M8-4MR-**SH-M8-4FR-PUR	4	T4062224004-00X
		FIXED: -10°C~80°C FLXIBLE: -5°C~80°C	BLACK	PVC (UL)	RPC-M8-4MR-**SH-M8-4FR-PVC	4	T4062214004-00X
CABLE CHARACTERISTIC	LENGTH "L"	RECOMMEND OPERATION TEMPERATURE FOR CABLE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	PART NUMBER
	THIS DRAWING IS A CONTROLLED DOCUMENT.						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN Nick Pan 24FEB2016 CHK Kobby Zhao 24FEB2016 APVD Xiang Xu 24FEB2016			
		0 PLC ± 1 PLC ±0.50 2 PLC ±0.35 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-106140			
MATERIAL TBD		FINISH -		APPLICATION SPEC -			
				WEIGHT -		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1	
				REV B			

TE Connectivity

M8 CABLE ASSEMBLY SHIELDED TYPE
DOUBLE ENDED

SIZE A2

CAGE CODE -

DRAWING NO. C-T40622X400X00X

RESTRICTED TO -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4062224003-001](#)