




VIEW A

T40622X4003-00X

PIN4 BLACK

PIN1 BROWN

PIN3 BLUE

T40622X4004-00X

PIN2 WHITE

PIN4 BLACK

PIN1 BROWN

PIN3 BLUE

VIEW B

PIN4 BLACK

PIN3 BLUE

PIN1 BROWN

PIN4 BLACK

PIN2 WHITE

PIN3 BLUE

PIN1 BROWN

TABLE 1

TECHNICAL DATA	T40622X4003-00X	T40622X4004-00X
RATED VOLTAGE	60V	30V
RATED CURRENT	3A	
POLLETION DEGREE	3	
OVERVOLTAGE CATEGORY	II	
MATERIAL GROUP	II	
DEGREE OF PROTECTION	IP67	

RUBBER	O-RING	8	
BALCK COLOR	PA66	HOUSING	7
GOLD FLASH	COPPER ALLOY	CONTACT	6
	COPPER ALOY	SHIELDING	5
BLUE COLOR	POLYURETHANE	OVER-MOLDING	4
-	COPPER ALLOY	COUPLING NUT	3
BALCK COLOR	PA66	HOUSING	2
GOLD FLASH	COPPER ALLOY	CONTACT	1
COMMENTS	MATERIAL	DESCRIPITON	ITEM

WIRES: 0.25mm²
(24AWG)

STANDARD:
-001:0.5M
-002:1.0M
-003:1.5M
-004:3.0M
-005:5.0M
-006:7.0M
-007:10.0M
CUSTOMIZATION:
-XX0:XX.0 M
-XX5:XX.5 M
-99X: 0.X M

FIXED:
-25°C~80°C
FLXIBLE:
-10°C~80°C

FIXED:
-10°C~80°C
FLXIBLE:
-5°C~80°C

GRAY

BLACK

PUR
(UL)

PVC
(UL)

RPC-M8-4MR-**SH-M8-4FR-PUR

RPC-M8-3MR-**SH-M8-3FR-PUR

RPC-M8-4MR-**SH-M8-4FR-PVC

RPC-M8-3MR-**SH-M8-3FR-PVC

4

3

T4062224004-00X

T4062224003-00X

4

3

T4062214004-00X

T4062214003-00X

CABLE CHARACTERISTIC

LENGTH "L"

RECOMMEND OPERATION TEMPERATURE FOR CABLE

JACKET COLOR

JACKET MATERIAL

TYPE

POS.

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
TBD

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.50
2 PLC ±0.35
3 PLC ±
4 PLC ±

ANGLES ±

FINISH -

APVD 24FEB2016
Xiang Xu

PRODUCT SPEC
108-106140

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

DWN 24FEB2016
Nick Pan

CHK 24FEB2016
Kobby Zhao

APVD 24FEB2016
Xiang Xu

NAME
M8 CABLE ASSEMBLY SHIELDED TYPE DOUBLE ENDED

SIZE
A2

CAGE CODE
-

DRAWING NO
C-T40622X400X00X

RESTRICTED TO
-

SCALE 1:1

SHEET 1 OF 1

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4062214003-001](#)