

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

TE PN CODING:

T4162XXXX0XX-00X

THREAD M12X1
DOUBLE ENDED
SHIELDED

S1 TYPE:
1-MALE STRAIGHT
2-MALE 90°
3-FEMALE STRAIGHT
4-FEMALE 90°

S2 TYPE:
1-MALE STRAIGHT
2-MALE 90°
3-FEMALE STRAIGHT
4-FEMALE 90°

POLES:
02-INSERT 2 POS
03-INSERT 3 POS
04-INSERT 4 POS
05-INSERT 5 POS

CABLE TYPE
1-0.34mm²,PVC BLACK
2-0.34mm²,PUR GRAY

LENGTH:
STANDARD:
-001:0.5 M
-002:1.0 M
-003:1.5 M
-004:3.0 M
-005:5.0 M
-006:7.0 M
-007:10.0 M
CUSTOMIZATION:
-XX0:XX.0 M
-XX5:XX.5 M
-99X: 0.X M
-98X:WITH SPECIAL KEY
POSITION
981:0.5M,
982:1.0M...

TE TYPE CODING:

RPC-M12-XXX-**SH-M12-XXX-PXX

RPC SERIES

S1 CONNECTOR TYPE:
M12X1 A-CODE
CONNECTOR

S1 TYPE:
2MS-2CON,MALE STRAIGHT
3MS-3CON,MALE STRAIGHT
4MS-4CON,MALE STRAIGHT
5MS-5CON,MALE STRAIGHT
2MR-2CON,MALE 90°
3MR-3CON,MALE 90°
4MR-4CON,MALE 90°
5MR-5CON,MALE 90°
5MRS-5CON,MALE 90°,WITH SPECIAL KEY POSITION

CABLE LENGTH:
0.5:0.5M,
1.0:1.0M,
1.5:1.5M,
3.0:3.0M,
5.0:5.0M,
7.0:7.0M,
10.0:10.0M,
...

S2 CONNECTOR TYPE:
M12X1 A-CODE
CONNECTOR

S2 TYPE:
2FS-2CON,FEMALE STRAIGHT
3FS-3CON,FEMALE STRAIGHT
4FS-4CON,FEMALE STRAIGHT
5FS-5CON,FEMALE STRAIGHT
2FR-2CON,FEMALE 90°
3FR-3CON,FEMALE 90°
4FR-4CON,FEMALE 90°
5FR-5CON,FEMALE 90°

CABLE TYPE
PVC-0.34mm²,PVC BLACK
PUR-0.34mm²,PUR GRAY

NOTE:

△. TECHNICAL DATA: SEE TABLE 1

△. CODE POSITION INDICATOR

△. RECOMMENDED TORQUE 0.6 Nm

4. CABLE ASSEMBLY TO BE PACKAGED IN POLYBAGS

△. LABEL CONTAINS: PN, DATE CODE...

△. CABLE LENGTH CODE:
STANDARD LENGTH:001...007
CUSTOMIZATION LENGTH: >1.0M;XX0 OR XX5
EXAMPLE:3.5M:035;15.0M:150...
<1.0M;99X
EXAMPLE:0.4M:994;...0.9M:999

注释:

△. 技术参数:参考表1

△. CODE位置指示

△. 推荐扭矩0.6 Nm

4. 线缆组件塑料袋包装

△. 标签包含: 产品编号, 日期代码...

△. 线缆长度编码:
标准长度:001...007
定制长度:>1.0M;XX0 或 XX5
例如:3.5M:035;15.0M:150...
<1.0M;99X
例如:0.4M:994;...0.9M:999

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

FIXED: -40℃~80℃ FLXIBLE: -25℃~80℃	GRAY	PUR (UL)	RPC-M12-5MR-**SH-M12-5FR-PUR	5	T4162224005-00X
			RPC-M12-4MR-**SH-M12-4FR-PUR	4	T4162224004-00X
			RPC-M12-3MR-**SH-M12-3FR-PUR	3	T4162224003-00X
			RPC-M12-2MR-**SH-M12-2FR-PUR	2	T4162224002-00X
FIXED: -10℃~80℃ FLXIBLE: -5℃~80℃	BLACK	PVC (UL)	RPC-M12-5MR-**SH-M12-5FR-PVC	5	T4162214005-00X
			RPC-M12-4MR-**SH-M12-4FR-PVC	4	T4162214004-00X
			RPC-M12-3MR-**SH-M12-3FR-PVC	3	T4162214003-00X
			RPC-M12-2MR-**SH-M12-2FR-PVC	2	T4162214002-00X
FIXED: -40℃~80℃ FLXIBLE: -25℃~80℃	GRAY	PUR (UL)	RPC-M12-5MR-**SH-M12-5FS-PUR	5	T4162223005-00X
			RPC-M12-4MR-**SH-M12-4FS-PUR	4	T4162223004-00X
			RPC-M12-3MR-**SH-M12-3FS-PUR	3	T4162223003-00X
			RPC-M12-2MR-**SH-M12-2FS-PUR	2	T4162223002-00X
FIXED: -10℃~80℃ FLXIBLE: -5℃~80℃	BLACK	PVC (UL)	RPC-M12-5MRS-**SH-M12-5FS-PVC	5	T4162213005-98X
			RPC-M12-5MR-**SH-M12-5FS-PVC	5	T4162213005-00X
			RPC-M12-4MR-**SH-M12-4FS-PVC	4	T4162213004-00X
			RPC-M12-3MR-**SH-M12-3FS-PVC	3	T4162213003-00X
			RPC-M12-2MR-**SH-M12-2FS-PVC	2	T4162213002-00X
FIXED: -40℃~80℃ FLXIBLE: -25℃~80℃	GRAY	PUR (UL)	RPC-M12-5MS-**SH-M12-5FR-PUR	5	T4162124005-00X
			RPC-M12-4MS-**SH-M12-4FR-PUR	4	T4162124004-00X
			RPC-M12-3MS-**SH-M12-3FR-PUR	3	T4162124003-00X
			RPC-M12-2MS-**SH-M12-2FR-PUR	2	T4162124002-00X
FIXED: -10℃~80℃ FLXIBLE: -5℃~80℃	BLACK	PVC (UL)	RPC-M12-5MS-**SH-M12-5FR-PVC	5	T4162114005-00X
			RPC-M12-4MS-**SH-M12-4FR-PVC	4	T4162114004-00X
			RPC-M12-3MS-**SH-M12-3FR-PVC	3	T4162114003-00X
			RPC-M12-2MS-**SH-M12-2FR-PVC	2	T4162114002-00X
FIXED: -40℃~80℃ FLXIBLE: -25℃~80℃	GRAY	PUR (UL)	RPC-M12-5MS-**SH-M12-5FS-PUR	5	T4162123005-00X
			RPC-M12-4MS-**SH-M12-4FS-PUR	4	T4162123004-00X
			RPC-M12-3MS-**SH-M12-3FS-PUR	3	T4162123003-00X
			RPC-M12-2MS-**SH-M12-2FS-PUR	2	T4162123002-00X
FIXED: -10℃~80℃ FLXIBLE: -5℃~80℃	BLACK	PVC (UL)	RPC-M12-5MS-**SH-M12-5FS-PVC	5	T4162113005-00X
			RPC-M12-4MS-**SH-M12-4FS-PVC	4	T4162113004-00X
			RPC-M12-3MS-**SH-M12-3FS-PVC	3	T4162113003-00X
			RPC-M12-2MS-**SH-M12-2FS-PVC	2	T4162113002-00X
CABLE TEMP.RANGE	JACKET COLOR	JACKET MATERIAL	TYPE	POS.	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

-

-

DWN
GAVIN WANG
25 JUL 2018

CHK
KEVIN HUANG
25 JUL 2018

APVD
CHRIS WANG
25 JUL 2018

PRODUCT SPEC
108-106140

APPLICATION SPEC
114-137144

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
M12X1 MALE TO FEMALE,XP
A-CODE,SHIELDED

SIZE
A2

CAGE CODE
-

DRAWING NO
©T4162XXX0XX00X

RESTRICTED TO
-

SCALE
2:1

SHEET
2 OF 2

REV
A1

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T4162213005-001](#)