


ECN #	APPRVD.	DATE	REV.
/			



SPECIFICATION

16Amp /40°C 50-60Hz


440VAC Phase to Phase

250VAC Phase to Neutral/Gnd

ATTENUATION

Comm.Mode - 70dB μ V at 100kHzDif.Mode - 70dB μ V at 100kHz

EQUIVALENT SCHEMATIC MEASURED AT 1kHz




Max. Leakage current at 10% unsymmetrical mains, each Line to Ground:

2,3mA at 120V 60Hz

4,0mA at 250V 50Hz

THIRD ANGLE PROJECTION



This document is proprietary to CORCOM INC. and is not to be reproduced nor used for manufacturing purposes except on CORCOM'S order or prior written consent.



844 E. ROCKLAND RD. LIBERVILLE IL 60048

RFI FILTER

CAD FILE: cde\prt\cd\F7741

SCALE: .45:1

DATE: 02-16-96

DRG. NO.

16FCD10

DRW. BY: MS

ORIG: MS

REV.

00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6609070-3](#)