

REV. 0

DCO 142908


COIL: @ 25°C
 RESISTANCE 3300 OHMS \pm 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.0 VDC
 MUST RELEASE 8.0 VDC MAX, 1.4 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX
 RELEASE TIME 7.5 MS MAX
 CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 1A 28 VDC RESISTIVE 100,000
 OPERATIONS

DR. B.D. 5/3/01 *CK Leary* 5/3/01

CI Technologies
 advanced control electronic solutions

CUST. GPL
 CUST. NO. M39016/16-044P REV.

JMSD RELAY

JMSCD-26XPS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1617128-5](#)