

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2007

© COPYRIGHT 2007

BY -



ALL RIGHTS RESERVED.

LOC
J



DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASED	22JUL2017	N.W	C.W



SCALE 1:1





RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1mm.

①.MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0), COLOR:BLACK
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

②.FINISH(ALL OVER):NICKEL PLATING 1.27μmMIN

③.FINISH(CONTACT AREA):TIN PLATING 1.0μmMIN AFTER ②

④.FINISH(CONTACT TAIL):TIN PLATING 2μmMIN AFTER ②
5.THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.



40	X	19	38.0	41.0	42.6	1-2271888-0
34	X	16	32.0	35.0	36.6	1-2271888-7
30	X	14	28.0	31.0	32.6	1-2271888-5
28	X	13	26.0	29.0	30.6	1-2271888-4
26	X	12	24.0	27.0	28.6	1-2271888-3
POS	KEY	n	A	B	C	PART NO

34POS(X-KEY):1-2271888-7

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 26JUN2017

CHK Ning Wang

26JUN2017

APVD Chris Wang

26JUN2017

PRODUCT SPEC

108-78298

APPLICATION SPEC


114-5377

WEIGHT

Customer Drawing

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.3, ±5°

0-PLC ±
1-PLC ±
2-PLC ±
3-PLC ±
4-PLC ±
ANGLES ±

FINISH

**TE**

TE Connectivity

NAME
DYNAMIC D1100D 2.0mmPITCH
HDR ASSY, H-TYPE
22-40POS

SIZE CAGE CODE DRAWING NO RESTRICTED TO
A300779 C-2271888

SCALE 1:1 SHEET 1 OF 2 REV A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2007

© COPYRIGHT 2007

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR













DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 2



26POS(X-KEY): I-2271888-3

28POS(X-KEY): I-2271888-4


30POS(X-KEY): I-2271888-5

40POS(X-KEY): I-2271888-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

MATERIAL

DWN 26JUL2017

Ning Wang

CHK 26JUL2017

Chris Wang

APVD 26JUL2017

Chris Wang

PRODUCT SPEC

108-78298

APPLICATION SPEC

114-5377

WEIGHT

Customer Drawing



TE Connectivity

NAME
DYNAMIC D1100D 2.0mmPITCH
HDR ASSY, H-TYPE
22-40POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2271888

SCALE 2:1

SHEET 2 OF 2

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2271888-4](#) [1-2271888-5](#) [1-2271888-7](#)