

[Help/Glossary](#)

AMP

Click to activate links to all other products

AMP

Active

Active

Previous

Next

Sales Information

AMP ACES

Step Search Screen

Related CAD Geometry

Related Documents

General Information

Pricing

Product Availability

■ Customer Drawing: 530743, Rev. G

Document Title: PIN HEADER ASSY, MINI-BOX,RIGHT
ANGLE, MILITARY

[172756.pdf](#) [172756.pdf](#) (112K)

The photographs and/or line drawings below are representative images of a product for viewing purposes only.

Product Photo

Brand:	AMP
Product Type:	Pin Header Assembly
Centerline Spacing (mm [in]):	1.27 [.050]
No. of Rows:	2
No. of Positions:	20
Grade:	Military
Post Styles:	Posted

Contact Material:	Brass
Contact Termination Area Plating:	Tin Lead over Nickel
Color:	Gray
Housing Material:	Liquid Crystal Polymer (LCP)

Post Size (mm [in]):	0.23 x 0.46 [.009 x .018]
Termination Post Length (mm [in]):	3.18 [.125]
Military Part Number:	M55302/117-01
Staggered:	No
Sealed:	No
Application:	PC Solder Mount
Strain Relief:	Without
Mount Angle:	Right Angle
PCB Mount Style:	Thru Hole
Gasket:	Without
Contact Mating Area Plating:	Gold (50)
Pin Protection:	Without
In-Line/Staggered Tails:	Staggered
Hybrid:	No
Jackscrews:	Without
Stabilizers:	Without

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Brands](#) | [Industries](#) | [Customer Service](#) | [About](#) | [Home](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M55302/117-02](#) [M55302/117-11](#)