



☐ 2mm Hard Metric PCB Connectors and Accessories (Z-PACK HS3)

 RoHS Compliant

Search for Parts

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
 General Info  Sales Info	 Pricing	 Tooling
 Assembly Subcontractors	 Product Availability	

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not suitable for lead free processing
Product Type:	Header Assembly
PCB Mount Angle:	Vertical
Module Type:	Center
No. of Rows:	6
No. of Positions:	60
Contact Style:	Short Tail
Solder Tail Plating:	Tin over Nickel
Guide Pin Style:	Compliant

Other Properties:	
RoHS/ELV Compliance History:	Always was compliant
Termination Post Length (mm [in]):	9.70 [0.382]
Housing Material:	Glass-Filled Polyester
Contact Material:	Phosphor Bronze
Contact Type:	Grounding, Signal
Contact Mating Area Length (mm [in]):	5.30 [0.209]
Contact Mating Area Plating:	Gold over Nickel
Post Type:	Compliant Post

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contain component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5120848-1](#)