


AMP

WIRE RANGE

26-22 AWG

STRANDED



1. WIRE INSULATION DIA 1.27[.050] TO 2.08[.082]
- 2 26-22 COMMERCIAL

-	4000	ON TAPE, REEL	2-323994-1
-	50	LOOSE PIECE, BOX	8-323994-2
-	50	LOOSE PIECE	2-323994-2
26-24 M7928/5-1 CLASS 1 & 2	50		323994

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE:  105°C	MILITARY P/N & CLASS PER MIL-T-7928		QTY	PACKAGE TYPE		PART NO		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER  1-800-522-6752		VOLTAGE RATING:  —	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± — ANGLES ± —	DR 9-28-93 S.S. GOULDEN	AMP  AMP Incorporated Harrisburg, PA 17105-3608	NAME  SPLICE, BUTT, PIDG* WIRE SIZE: 26-22 AWG				
	TOOLING ASSISTANCE CENTER  1-800-722-1111		CIRCULAR MIL AREA:  0.10-0.41mm² [202-810]		CHK 9-28-93 R. HERSEY						
	TOOLING INFORMATION		STRANDED		APPD 9-28-93 S. BORTNER						
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	COPPER PER ASTM B-152 NYLON, COLOR: YELLOW	APPD 9-28-93 M. ELLIS	SIZE B	CAGE CODE 00779	DRAWING NO C-323994	SCALE NTS	SHEET 1 OF 1	
1-800-526-5142		FINISH TIN PLATE PER MIL-T-10727		PRODUCT SPEC —	APPLICATION SPEC —						WEIGHT —

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M7928/5-1](#)