






1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED.
- ③ TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- ④ TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.



	OBSOLETE	TINNED	PHOS.BRZ..006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641610-5
			PHOS.BRZ..008 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641610-4
	OBSOLETE	TINNED	PHOS.BRZ..006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641610-3
			BE.CU..006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641610-2
		TINNED	BE.CU..006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-641610-1
		CONTACT FINISH	CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES		
	Ø PLC	± .-
	1 PLC	± .-
	2 PLC	± .-
	3 PLC	± .005
	4 PLC	± .-
	ANGLES	± 0°-30'
	FINISH	

MATERIAL SEE TABLE	SEE TABLE
-----------------------	-----------

DWN R BROWN		QBJAH01
C/K H WYNKOOP	17NOV00	Tyco Electronics Corporation Harrisburg, PA 17105
A/P/D H WYNKOOP	17NOV00	
NAME		
SOCKET ASSY, DIP, LADDER, RET LEG, 16 POS, DIPLOMATE™ DL -		
PRODUCT SPEC 108-1066		SIZE CAGE CODE DRAWING NO A1 00779 C=641610
APPLICATION SPEC 114-1049		
WEIGHT -		
CUSTOMER DRAWING		

SCALE 5:1	SHEET 1 OF 1	REV. W
-----------	--------------	--------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-641610-4](#)