




- 1 RECEPTACLE ACCEPTS A .008—.014 THICK I.C.LEAD.
- 2 TUBE LOADED FOR AUTOMATIC INSERTION.
- 3 BECU CONTACT —PLATED WITH TWO .000030 MIN THIK.
GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS,
BALENCE OF CONTACT NICKEL PLATED.
- 4 PHOS. BRZ CONTACT — PLATED WITH TWO .000015 MIN THK.
GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS,
BALENCE OF CONTACT NICKEL PLATED.
- 5 GLASS FILLED THERMOPLASTIC, 94V-0, BLACK

	2.300	23	2.395	48	1-1825376-4
	1.900	19	1.995	40	1-1825376-3
	1.300	13	1.395	28	1-1825376-2
	1.100	11	1.195	24	1-1825376-1
	2.300	23	2.395	48	1825376-4
	1.900	19	1.995	40	1825376-3
	1.300	13	1.395	28	1825376-2
	1.100	11	1.195	24	1825376-1
CONTACT & FINISH	DIM C	B SPCS	DIM A	POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN E.S.VISWESWARA 22APR05 DWG K.WRIGHT APP'D --		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLG ± 1 PLG ± 2 PLG ± 3 PLG ±.005 4 PLG ± ANGLES ± 0°30' FINISH		NAME DIP SOCKET ASSY, LADDER, DIPLOMATE, RET. LEAD .600 CL, LEAD FREE	
MATERIAL SEE TABLE		PRODUCT SPEC 108-1066 APPLICATION SPEC 114-1049 WEIGHT --		SIZE CAGE CODE DRAWING NO A1 00779 C=1825376 RESTRICTED TO --	
SEE TABLE		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1825376-3](#)