




THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	19
© COPYRIGHT 19	BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.	

LOC	DIST			REVISIONS							
		AD	39	P	F	ZONE	LTR	DESCRIPTION	DATE	DNW	APVD
						D		PLASTIC MATERIAL SUPPLIER CHANGED FOR HOUSING	07MAY2021	SB	KJK



$\phi 0.38[.015]$ M X
TYP AT POST TIPS



- 1 HSG: GLASS FILLED NYLON, COLOR - BLACK
- 2 POSTS: PHOSPHOR BRONZE
- 3 FINISH: 0.00254-0.00508 [.000100-.000200] TIN-LEAD OVER 0.00127 [.000050] MIN NICKEL ON ENTIRE POST
- 4 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 5 RETENTION FEATURE FOR 1.57 [.062] THICK PC BOARD PER MANUFACTURER'S DESIGN AND CUSTOMER'S APPROVAL. (SEE TABLE FOR LOCATIONS)

1, 6	2	14.83 [.584]	4	5	6	104836-3
1, 3, 5, 7, 13, 15, 17, 18	2, 4, 6, 8, 10, 12, 14, 16	45.31 [.1784]	17	10	18	104836-2
OBsolete	OBsolete					
NONE	2, 4, 5, 7, 9	24.99 [.984]	9	5	10	104836-1
RETENTION FEATURE LOCATION	POST NUMBER OMITTED	B	A	NO OF ACTIVE POSN	NO OF POSN	PART NUMBER

PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC \pm 0.13 [.005] 3 PLC DEC \pm - ANGLES \pm -	DR 2-24-92 S. SHUEY	CHK 2-28-92 R. FEIDT	APPD 2-28-92 R. FEIDT
MATERIAL HOUSING: 1	APPD 2-28-92 R. FEIDT	PRODUCT SPEC -	NAME
POSTS: 2	APPD 2-28-92 R. FEIDT	POSTS: 2	TE Connectivity
FINISH 3	APPLICATION SPEC -	SIZE C	CAGE CODE 00779
	WEIGHT -	SCALE 4:1	DRAWING NO 104836
			SHEET 1 OF 1 REV D

METRIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104836-3](#)