




BRINGTON	18-6-93		TE Connectivity				
CMCICH	24-6-93						
	24-6-93						
PLER SPEC	NAME	ASSEMBLY, HEADER, RIGHT ANGLE, DOUBLE ROW, AMPMODU 50/50 GRID CONNECTOR					
3-1332							
ON SPEC							
4-7010							
-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
FORMER DRAWING	A1	00779	C-104894	-			
	SCALE	5:1	SHEET	1	OF	1	
			REV	K			



- | | | | | | | | | | |
|--------------------------------------|---|---------------------------|------------------------------|------------------------------|------------------------------|------------------------------|------------------------------|-----------------------|-----------------------|
| | <div><div>9</div><div>5</div><div>7</div></div> | 49 | <div>71.12
[2.800]</div> | <div>62.87
[2.475]</div> | 99 | <div>73.15
[2.880]</div> | 100 | 6-104894-0 | |
| <div><div>10</div><div>9</div></div> | OBSOLETE | <div>5</div> <div>7</div> | 44 | <div>64.77
[2.550]</div> | <div>56.52
[2.225]</div> | 89 | <div>66.80
[2.630]</div> | 90 | 5-104894-9 |
| <div><div>10</div><div>9</div></div> | OBSOLETE | <div>5</div> <div>7</div> | 39 | <div>58.42
[2.300]</div> | <div>50.17
[1.975]</div> | 79 | <div>60.45
[2.380]</div> | 80 | 5-104894-8 |
| | <div>9</div> <div>5</div> <div>7</div> | 34 | <div>52.07
[2.050]</div> | <div>43.82
[1.725]</div> | 69 | <div>54.10
[2.130]</div> | 70 | 5-104894-7 | |
| | <div>9</div> <div>5</div> <div>7</div> | 29 | <div>45.72
[1.800]</div> | <div>37.47
[1.475]</div> | 59 | <div>47.75
[1.880]</div> | 60 | 5-104894-6 | |
| | <div>9</div> <div>5</div> <div>7</div> | 24 | <div>39.37
[1.550]</div> | <div>31.12
[1.225]</div> | 49 | <div>41.40
[1.630]</div> | 50 | 5-104894-5 | |
| | <div>9</div> <div>5</div> <div>7</div> | 19 | <div>33.02
[1.300]</div> | <div>24.77
[.975]</div> | 39 | <div>35.05
[1.380]</div> | 40 | 5-104894-4 | |
| | <div>9</div> <div>5</div> <div>7</div> | 14 | <div>26.67
[1.050]</div> | <div>18.42
[.725]</div> | 29 | <div>28.70
[1.130]</div> | 30 | 5-104894-3 | |
| | <div>9</div> <div>5</div> <div>7</div> | 9 | <div>20.32
[.800]</div> | <div>12.07
[.475]</div> | 19 | <div>22.35
[.880]</div> | 20 | 5-104894-2 | |
| | <div>9</div> <div>5</div> <div>7</div> | 4 | <div>13.97
[.550]</div> | <div>5.72
[.225]</div> | 9 | <div>16.00
[.630]</div> | 10 | 5-104894-1 | |
| | <div>6</div> <div>5</div> <div>7</div> | 24 | <div>39.37
[1.550]</div> | <div>31.12
[1.225]</div> | 49 | <div>41.40
[1.630]</div> | 50 | 1-104894-5 | |
| | <div>6</div> <div>5</div> <div>7</div> | 14 | <div>26.67
[1.050]</div> | <div>18.42
[.725]</div> | 29 | <div>28.70
[1.130]</div> | 30 | 1-104894-3 | |
| | <div>1</div> <div>3</div> | 49 | <div>71.12
[2.800]</div> | <div>62.87
[2.475]</div> | 99 | <div>73.15
[2.880]</div> | 100 | 1-104894-0 | |
| | <div>1</div> <div>3</div> | 44 | <div>64.77
[2.550]</div> | <div>56.52
[2.225]</div> | 89 | <div>66.80
[2.630]</div> | 90 | 104894-9 | |
| | <div>1</div> <div>3</div> | 39 | <div>58.42
[2.300]</div> | <div>50.17
[1.975]</div> | 79 | <div>60.45
[2.380]</div> | 80 | 104894-8 | |
| | <div>1</div> <div>3</div> | 34 | <div>52.07
[2.050]</div> | <div>43.82
[1.725]</div> | 69 | <div>54.10
[2.130]</div> | 70 | 104894-7 | |
| | <div>1</div> <div>3</div> | 29 | <div>45.72
[1.800]</div> | <div>37.47
[1.475]</div> | 59 | <div>47.75
[1.880]</div> | 60 | 104894-6 | |
| | <div>1</div> <div>3</div> | 24 | <div>39.37
[1.550]</div> | <div>31.12
[1.225]</div> | 49 | <div>41.40
[1.630]</div> | 50 | 104894-5 | |
| SUPERCEDED | <div>1</div> <div>3</div> | 19 | <div>33.02
[1.300]</div> | <div>24.77
[.975]</div> | 39 | <div>35.05
[1.380]</div> | 40 | 1-104894-4 | |
| | <div>1</div> <div>3</div> | 14 | <div>26.67
[1.050]</div> | <div>18.42
[.725]</div> | 29 | <div>28.70
[1.130]</div> | 30 | 104894-3 | |
| | <div>1</div> <div>3</div> | 9 | <div>20.32
[.800]</div> | <div>12.07
[.475]</div> | 19 | <div>22.35
[.880]</div> | 20 | 104894-2 | |
| | <div>1</div> <div>3</div> | 4 | <div>13.97
[.550]</div> | <div>5.72
[.225]</div> | 9 | <div>16.00
[.630]</div> | 10 | 104894-1 | |



BASIC DIMENSIONS FOR
ODD NO OF SPACES
(SEE TABLE)

BASIC DIMENSIONS FOR
EVEN NO OF SPACES
(SEE TABLE)

DETAIL R

RECOMMENDED BOARD LAYOUT

SCALE 5:1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-104894-0](#)