








PAY ATTENTION !
DIFFERENT LOCKING LATCHES



△31 ONLY FOR 1-2178029-3, TOLERANCE IS +0.15/-0.2

4805 (3/11)

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-			SEE SHEET 1			

- ONLY FOR 2322912-3. TOLERANCE IS +0.1/-0.15
- ONLY FOR 2322912-6. 1-2364737-1. TOLERANCE IS -0.30
- CANDIDATE PRELIMINARY P/N. NOT YET OFFICIAL. ONLY FOR DISCUSSION. NOT YET RELEASED FOR PRODUCTION.
- DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL.

	5-1241965-5	5	05-B	25	20	NATURAL	UL94-V0 & GWEPT 750 no flame 	E	
	1-2364737-1	11	11-B	55	50	BLUE	UL94-V0 & GWEPT 750 no flame 	B	
	2364737-9	9	-	45	40	BLUE		C	
	2364737-5	5	-	25	20	BLUE		B	
	1-2364737-2	2	02-B	10	5	BLUE		B	
	2364737-2	2	02-A	10	5	BLUE		B	
	2322912-8	8	08-D	40	35	BLUE	PA66 UL94 V0 GWT 750	B	
	2322912-6	6	06-D	30	25	BLUE		B	
	2322912-3	3	-	15	10	YELLOW		B	
	2-2322912-2	2	02-A	10	5	NATURE		B	
	1-2322912-2	2	02-G	10	5	BLUE		B	
	2322912-2	2	02-C	10	5	GREY	PA66 UL94 V0 GWT 750 CT1350	B	
	5-1241965-7	7	07-C	35	30	NATURAL		E	
	4-1241965-7	7	-	35	30	NATURAL		E	
	5-1241965-5	5	05-B	25	20	NATURAL		E	
	5-1241965-4	4	-	20	15	NATURAL		E	
	4-1241965-4	4	-	20	15	NATURAL		E	
	3-1241965-4	4	-	20	15	NATURAL		E	
	2-1241965-4	4	-	20	15	NATURAL		E	
	1-1241965-4	4	04-C	20	15	NATURAL		E	
	8-1241965-2	2	02-C	10	5	NATURAL		E	
	2-1241965-2	2	-	10	5	NATURAL		E	
	PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
	SPECIAL VERSION: UL94 V0 & GW T 750								

KEYING PLAN SEE SHEET 2 OF 4

2345754-1	2	02-C	10	5	NATURAL	PA66 UL94 V0	E	
PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
SPECIAL VERSION: UL94 V0								

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN
Kishor M
CHK
K. Munz
APVD
Th. Klenner

18JUL2017
07-NOV-06
07-NOV-06

TE Connectivity

NAME

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

PRODUCT SPEC
108-18049

APPLICATION SPEC
-

WEIGHT
-

Customer Drawing

SIZE
A1

CAGE CODE
00779

DRAWING NO
1241965

RESTRICTED TO
-




SCALE
5:1

SHEET
3


OF
4

REV
B54


SPECIAL VERSIONS
9 POS STD. TIMER HSG. WITH TANGLING PROTECTION









ONLY FOR 0-964702-2





SPECIAL VERSION
8 POS SPECIAL STD. TIMER HSG.



SWAGED KEYING RIB



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN: Kishor M 18JUL2017		 TE Connectivity		
DIMENSIONS:			CHK: K. Munz 07-NOV-06				
mm			APVD: Th. Klenner 07-NOV-06		NAME		
			TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		2-12 POS. STANDARD TIMER HSG WITH EXTERIOR LOCKING		
			PRODUCT SPEC				
			108-18049				
			APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
			108-18049				
			APPLICATION SPEC				
MATERIAL			WEIGHT		A1 00779 ©=1241965 -		
SEE TABLES			Customer Drawing		SCALE 5:1 SHEET 4 of 4 REV B54		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1241965-6](#)