









PAY ATTENTION !
DIFFERENT LOCKING LATCHES



ADDITIONAL NOTES SEE 3 OF SHEET 4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG Kishor M CHK K. Munz 18JUL2017 07-NOV-06 07-NOV-06		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 0-PLC ±0.1 1-PLC ±0.1 2-PLC ±0.1 3-PLC ±0.001 4-PLC ±0.001 ANGLES ±		NAME Th. Klenner PRODUCT SPEC 108-18049-1 APPLICATION SPEC -	
		2-12 POS. STANDARD TIMER HSG WITH EXTERIOR LOCKING		SIZE A	
MATERIAL SEE TABLES		WEIGHT -		CASE CODE 00779	
FINISH -		DRAWING NO C=124 1965		RESTRICTED TO -	
Customer Drawing				SCALE	5:1
				SHEET	1 of 4
				REV	B55

LOC	DIST	REVISIONS					
		P	LYR	DESCRIPTION	DATE	DWN	APVD
A1	-			SEE SHEET 1			

- 32

ONLY FOR 2322912-3. TOLERANCE IS +0.1/-0.15
- 33

ONLY FOR 2322912-6. 1-2364737-1. TOLERANCE IS -0.30
- 34


CANDIDATE PRELIMINARY P/N. NOT YET OFFICIAL. ONLY FOR DISCUSSION. NOT YET RELEASED FOR PRODUCTION.
- 35

DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL.

	5-1241965-5	5	05-B	25	20	NATURAL	UL94-V0 & GW EPT 750 no flame 34 35	E	32 33
									32 33
36 37	1-2364737-1	11	11-B	55	50	BLUE	UL94-V0 & GW EPT 750 no flame 34 35	B	32 33
	2364737-9	9	-	45	40	BLUE		C	32 33
	2364737-5	5	-	25	20	BLUE		B	32 33
	1-2364737-2	2	02-B	10	5	BLUE		B	32 33
	2364737-2	2	02-A	10	5	BLUE		B	32 33
									32 33
	2322912-8	8	08-D	40	35	BLUE	PA66 UL94 V0 GW T 750	B	32 33
	2322912-6	6	06-D	30	25	BLUE		B	32 33
	2322912-3	3	-	15	10	YELLOW		B	32 33
	2-2322912-2	2	02-A	10	5	NATURE		B	32 33
	1-2322912-2	2	02-G	10	5	BLUE		B	32 33
38	2322912-2	2	02-C	10	5	GREY		B	32 33
									32 33
	5-1241965-7	7	07-C	35	30	NATURAL	PA66 UL94 V0 GW T 750 CT1350	E	32 33
	4-1241965-7	7	-	35	30	NATURAL		E	32 33
39	5-1241965-5	5	05-B	25	20	NATURAL		E	32 33
	5-1241965-4	4	-	20	15	NATURAL		E	32 33
	4-1241965-4	4	-	20	15	NATURAL		E	32 33
40	3-1241965-4	4	-	20	15	NATURAL		E	32 33
	2-1241965-4	4	-	20	15	NATURAL		E	32 33
	1-1241965-4	4	04-C	20	15	NATURAL		E	32 33
	8-1241965-2	2	02-C	10	5	NATURAL		E	32 33
	2-1241965-2	2	-	10	5	NATURAL		E	32 33
	PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
	SPECIAL VERSION: UL94 V0 & GW T 750								

KEYING PLAN SEE SHEET 2 OF 4

2345754-1	2	02-C	10	5	NATURAL	PA66 UL94 V0	E	32 33
PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
SPECIAL VERSION: UL94 V0								



Printed on 23 Dec 2021 14:07 (W. Europe Standard Time) from TEL00317

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-928247-1](#)