





⚠

JACK INTERFACE PER DIN 72594-1,
ROAD VEHICLES - RADIO FREQUENCY INTERFACE - DIMENSIONS AND ELECTRICAL
REQUIREMENTS.

2.

JACK SUBASSEMBLY WILL ACCEPT MI7/28-RG58 COAXIAL CABLE PER MIL-C-17 AND
LOW LOSS RG58 TYPE ANDREW CORPORATION PART NUMBER 910046A000.
ALSO, ACCEPTS MINI 59 TYPE CABLE.

3.


SEE INSTRUCTION SHEET 408-10028.

4.

PIN CONTACT 1438890-7 MUST BE PURCHASED SEPARATELY FOR USE WITH RG58 AND
RG58LL CABLE. PIN CONTACT 1438890-8 MUST BE PURCHASED SEPARATELY FOR USE
WITH MINI 59 CABLE.

RECOMMENDED STRIP LENGTH DIMENSIONS
SCALE: NTS

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	ECO-14-009247	18JUN2014	KP	LLV



PER DETAIL Y	PER DETAIL K	K	GRAY	1438894-2	CURRY	1-1438887-0	6-1438911-0
PER DETAIL Y	PER DETAIL H	H	GRAY	1438894-2	HEATHER VIOLET	1438887-8	5-1438911-8
PER DETAIL Y	PER DETAIL G	G	GRAY	1438894-2	BLUE GRAY	1438887-7	5-1438911-7
PER DETAIL Y	PER DETAIL F	F	GRAY	1438894-2	NUT BROWN	1438887-6	5-1438911-6
PER DETAIL Y	PER DETAIL E	E	GRAY	1438894-2	LEAF GREEN	1438887-5	5-1438911-5
PER DETAIL Y	PER DETAIL D	D	GRAY	1438894-2	CLARET VIOLET	1438887-4	5-1438911-4
PER DETAIL Y	PER DETAIL C	C	GRAY	1438894-2	SIGNAL BLUE	1438887-3	5-1438911-3
PER DETAIL Y	PER DETAIL B	B	GRAY	1438894-2	SIGNAL WHITE	1438887-2	5-1438911-2
PER DETAIL Y	PER DETAIL A	A	GRAY	1438894-2	JET BLACK	1438887-1	5-1438911-1
PER DETAIL X	PER DETAIL K	K	RED	1438888-1	CURRY	1-1438887-0	1-1438911-0
PER DETAIL X	PER DETAIL H	H	RED	1438888-1	HEATHER VIOLET	1438887-8	1438911-8
PER DETAIL X	PER DETAIL G	G	RED	1438888-1	BLUE GRAY	1438887-7	1438911-7
PER DETAIL X	PER DETAIL F	F	RED	1438888-1	NUT BROWN	1438887-6	1438911-6
PER DETAIL X	PER DETAIL E	E	RED	1438888-1	LEAF GREEN	1438887-5	1438911-5
PER DETAIL X	PER DETAIL D	D	RED	1438888-1	CLARET VIOLET	1438887-4	1438911-4
PER DETAIL X	PER DETAIL C	C	RED	1438888-1	SIGNAL BLUE	1438887-3	1438911-3
PER DETAIL X	PER DETAIL B	B	RED	1438888-1	SIGNAL WHITE	1438887-2	1438911-2
PER DETAIL X	PER DETAIL A	A	RED	1438888-1	JET BLACK	1438887-1	1438911-1
ASSEMBLY	KEYING	CODING	LOCK COLOR	LOCK PART NUMBER	HOUSING COLOR	JACK HOUSING PART NUMBER	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.J. HARDY CHK J.W. HALL APVD J.W. HALL	03JAN2005 26JAN2005 26JAN2006	NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
mm		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC	
MATERIAL		FINISH		WEIGHT	
-		-		-	
-		-		CUSTOMER DRAWING	

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	-	C=1438911	-
SCALE 4:1		SHEET 1 OF 2	REV F2

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-

CODING RIB A


CODING RIB B1



DETAIL A
SCALE 5:1

CODING RIB A

CODING RIB B2




DETAIL B
SCALE 5:1

CODING RIB A


CODING RIB C

CODING RIB D




DETAIL C
SCALE 5:1

CODING RIB A



DETAIL D
SCALE 5:1


CODING RIB B1



DETAIL E
SCALE 5:1

CODING RIB B2


CODING RIB B1



DETAIL F
SCALE 5:1

CODING RIB C


CODING RIB B1



DETAIL G
SCALE 5:1

CODING RIB D

CODING RIB B2




DETAIL H
SCALE 5:1

CODING RIB C

CODING RIB D

CODING RIB C



DETAIL K
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.J. HARDY	03JAN2005	TE Connectivity	
		CHK J.W. HALL	26JAN2005		
DIMENSIONS:		APVD J.W. HALL	26JAN2006	NAME	JACK KIT, UNASSEMBLED, 1 POSITION, MINI 59, RG-58 OR RG-58 LL, FAKRA, SMB
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC		APPLICATION SPEC	
		1 PLC		SIZE	A1
		2 PLC		CAGE CODE	-
		3 PLC		DRAWING NO	C=1438911
		4 PLC		RESTRICTED TO	-
		ANGLES		SCALE	4:1
		FINISH		SHEET	2 OF 2
MATERIAL		WEIGHT		REV	F2
-		-		CUSTOMER DRAWING	
-		-			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1438911-4](#)