








PCB LAYOUT: COMPONENT SIDE
RECOMMENDED BOARD THICKNESS 1.60 [1.60]



| | | | | |
|---|-----|----------------------|--------------|-------------|
|  | 6 | 8.4±0.1 [.33±.004] | 13.8 [.54] | 5-1586041-6 |
| | 2 | | 5.4 [.21] | 1586041-2 |
| | 4 | 4.2±0.1 [.17±.004] | 9.6 [.38] | 1586041-4 |
| | 6 | 8.4±0.1 [.33±.004] | 13.8 [.54] | 1586041-6 |
| | 8 | 12.6±0.1 [.50±.004] | 18.0 [.71] | 1586041-8 |
| | 10 | 16.8±0.1 [.66±.004] | 22.2 [.87] | 1-1586041-0 |
| | 12 | 21.0±0.2 [.83±.008] | 26.4 [1.04] | 1-1586041-2 |
| | 14 | 25.2±0.2 [.99±.008] | 30.6 [1.21] | 1-1586041-4 |
| | 16 | 29.4±0.2 [1.16±.008] | 34.8 [1.37] | 1-1586041-6 |
| | 18 | 33.6±0.2 [1.32±.008] | 39.0 [1.54] | 1-1586041-8 |
| | 20 | 37.8±0.2 [1.49±.008] | 43.2 [1.70] | 2-1586041-0 |
| | 22 | 42.0±0.2 [1.65±.008] | 47.4 [1.87] | 2-1586041-2 |
| | 24 | 46.2±0.2 [1.82±.008] | 51.6 [2.03] | 2-1586041-4 |
| REMARKS | POS | A | B±0.35[±.01] | PART NUMBER |

| | | | | | | | |
|---|--|---|--|---|-----------|---|---------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN S. HOOVER 18-SEP-2002 | | <div>TE Connectivity</div> | | | |
| | | CHK D. COLEY 18-SEP-2002 | | | | | |
| DIMENSIONS: mm [INCHES] | | TOLERANCES UNLESS OTHERWISE SPECIFIED: | | NAME | | | |
|  | | D. COLEY 18-SEP-2002 | | | | | |
| | | PRODUCT SPEC 108-2112 | | RIGHT ANGLE HEADER, WITHOUT PEGS VAL-U-LOK(TM) | | | |
| | | APPLICATION SPEC 114-13172 | | | | | |
| MATERIAL | | FINISH | | SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|  | |  | | A2 | 00779 |  1586041 | — |
| CUSTOMER DRAWING | | | | | | SCALE | SHEET |
| | | | | | | N/A | 1 of 1 |
| | | | | | | REV | B6 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1586041-0](#)