

20


RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.  
BY TYCO ELECTRONICS CORPORATION

COPYRIGHT 20

| LOC | DIST | REVISIONS |     |               |           |     |      |
|-----|------|-----------|-----|---------------|-----------|-----|------|
| HV  | 00   | P         | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|     |      |           | A1  | ECO-10-022743 | 05NOV2010 | DR  | DR   |
|     |      |           | A2  | ECO-11-024207 | 02DEC2011 | DR  | DR   |
|     |      |           | A3  | ECO-13-012771 | 08AUG2013 | DR  | DR   |
|     |      |           |     |               |           |     |      |




SECTION A - A

1 MATERIAL:  
TYPE: COPPER ALLOY

2. FINISH:  
UNDERPLATE TYPE: NICKEL  
TOP PLATE TYPE: TIN

3. PARTS MUST BE FREE OF EXCESSIVE BURRS,  
CRACKS, OR OTHER VISUAL IMPERFECTIONS  
THAT MAY AFFECT FIT FORM OR FUNCTION



SCALE 2:1

|       |       |        |     |           |
|-------|-------|--------|-----|-----------|
| 13.93 | 12.13 | 1.26g  | A   | 1587724-3 |
| 12.93 | 11.13 | 1.15g  | A   | 1587724-2 |
| 11.93 | 10.13 | 1.00g  | A   | 1587724-1 |
| F     | E     | WEIGHT | REV | PART NO   |

|                                                                           |  |                                            |               |  |        |  |
|---------------------------------------------------------------------------|--|--------------------------------------------|---------------|--|--------|--|
| DIMENSIONS:<br>mm                                                         |  | DWN<br>D SIMPSON<br>02JUN2008              | MATERIAL<br>1 |  | FINISH |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                 |  | CHK<br>A TYLER<br>02JUN2008                |               |  |        |  |
| 0 PLC ±<br>1 PLC ±0.15<br>2 PLC ±0.10<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±1° |  | APVD<br>J. BOLEWITZ<br>02JUN2008           |               |  |        |  |
| PRODUCT SPEC                                                              |  | NAME<br>OUTER FERRULE<br>HVA280 MULTI-CORE |               |  |        |  |
| APPLICATION SPEC                                                          |  | SIZE<br>A 4                                |               |  |        |  |
| WEIGHT<br>SEE TABLE                                                       |  | CAGE CODE<br>00779                         |               |  |        |  |
| CUSTOMER DRAWING                                                          |  | DRAWING NO<br>C-1587724                    |               |  |        |  |
|                                                                           |  | RESTRICTED TO                              |               |  |        |  |
|                                                                           |  | SCALE 8:1 SHEET 1 OF 1 REV A3              |               |  |        |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1587724-2](#)