






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECO-20-013571	17FEB2021	SR	JB



2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y





**PRODUCT MARKING
DETAIL A**

PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36

6 1634200-2 SHOWN ON-OFF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712	2-4-07	 TE Connectivity Ltd.	
		CHK —	—		
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED	
		APVD —			
		PRODUCT SPEC —		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		APPLICATION SPEC —			
		WEIGHT A2			
		CUSTOMER DRAWING			
		SCALE			
MATERIAL —		FINISH —		00779	
				C=1634200	
				SHEET	
				1 OF 7	
				REV	
				F	




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

C


B

A




2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM





PRODUCT MARKING
DETAIL A

PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36

 OBSOLETE
~~1634200-8~~ SHOWN ON-OFF ILLUMINATED




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 2-4-07 SA008712	 TE Connectivity Ltd.			
DIMENSIONS: mm		CHK -				
		APVD -	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED			
		PRODUCT SPEC -	SIZE CAGE CODE DRAWING NO A2 00779 C=1634200			
MATERIAL -		FINISH -	RESTRICTED TO -			
		TOLERANCES, UNLESS OTHERWISE SPECIFIED:	SCALE 3:1 SHEET 2 OF 7 REV F			
		0 PLC ± -	CUSTOMER DRAWING			
		1 PLC ± -				
		2 PLC ± -				
		3 PLC ± -				
		4 PLC ± -				
		ANGLES ± -				

1634200

B


A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM



PRODUCT MARKING
DETAIL A

PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36

8 1-1634200-2 SHOWN ON-ON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 2-4-07 SA008712	TE Connectivity Ltd.			
DIMENSIONS: mm		CHK -				
		APVD -	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED			
		PRODUCT SPEC -	SIZE CAGE CODE DRAWING NO A2 00779 C=1634200			
MATERIAL -		FINISH -	RESTRICTED TO -			
		TOLERANCES, UNLESS OTHERWISE SPECIFIED:	SCALE 3:1 SHEET 3 OF 7 REV F			
		0 PLC ± -	CUSTOMER DRAWING			
		1 PLC ± -				
		2 PLC ± -				
		3 PLC ± -				
		4 PLC ± -				
		ANGLES ± -				

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




D

C


B

A

SWITCH FRAME
ROCKER




PANEL CUT OUT




2.00–3.00	20.20	22.20
1.25–2.00	19.60	22.20
0.75–1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM



**PRODUCT MARKING
DETAIL A**

**PRE
10A 125VAC, 6A 250VAC**



TYCO ELECTRONICS LOGO
PER TEC-202-36

9 1-1634200-7 SHOWN ON-OFF-ON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 2-4-07 SA008712	TE Connectivity Ltd.		
DIMENSIONS: mm		CHK -			
		APVD -	NAME		
		PRODUCT SPEC -	POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED		
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO
		WEIGHT -	A2	00779	C=1634200
MATERIAL -	FINISH -	CUSTOMER DRAWING	SCALE 3:1	SHEET 4 OF 7	REV F

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B


A

D


C

B

A




PANEL CUT OUT



2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM



PRODUCT MARKING DETAIL A

PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36

10 2-1634200-3 SHOWN ON-OFF-(ON)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	2-4-07	TE Connectivity Ltd.	
		CHK	-		
DIMENSIONS:		APVD	-	NAME	
mm		PRODUCT SPEC	-		
		APPLICATION SPEC	-	SIZE	
		WEIGHT	-		
MATERIAL		CUSTOMER DRAWING	-	CAGE CODE	00779
FINISH		SCALE	3:1	DRAWING NO	C=1634200
		SHEET	5 of 7	RESTRICTED TO	-
		REV	F		




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D


C

B

A



2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y




PRODUCT MARKING
DETAIL A

PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36

11 2-1634200-6 SHOWN (ON)-OFF-(ON)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 2-4-07 SA008712		 TE Connectivity Ltd.							
DIMENSIONS: mm		CHK —									
		APVD —		NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED							
		PRODUCT SPEC —									
		APPLICATION SPEC —									
		WEIGHT —									
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		FINISH —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
0 PLC ± —		—		A2		00779		C=1634200		—	
1 PLC ± —		—		CUSTOMER DRAWING							
2 PLC ± —											
3 PLC ± —											
4 PLC ± —											
ANGLES ± —		—		SCALE 3:1		SHEET 6 of 7		REV F			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

ALCOSWITCH PART NUMBER

1 MATERIALS:
HOUSING FRAME: NYLON 66.
ACTUATOR: NYLON 66/ PC(ILLUMINATED)
TERMINALS C1100R-1/2H WITH SILVER PLATED CONTACTS
AgALLOY

2 FINISH:
TERMINAL, ACTIVE CONTACTOR: 1.0µm [.000039] SILVER
PLUNGER: 3.0µm[.000118] NICKEL

3 ELECTRICAL SPECIFICATIONS:
CONTACT RESISTANCE : 50m ohm Max
DIELECTRIC STRENGTH : AC 1500V, 1 MINUTE
OPERATION TEMPERATURE: -20°C~85°C
INSULATION R: DC 500V 100M ohm MIN

4 CURRENT AND VOLTAGE 10A@125VAC/6A@250VAC

5 ELECTRICAL RATINGS, APPROVED AGENCY LOGOS,
TE LOGO PER TEC-202-36 APPROXIMATELY AS SHOWN
AND PART NUMBER CAN APPEAR ON EITHER SIDE
(FOR FULL DETAIL SEE INDIVIDUAL DRAWING)

6 ON-OFF, WITH OPAQUE, SINGLE-COLOR ROCKER BUTTON.

7 ON-OFF, WITH TRANSPARENT, LAMP-ILLUMINATED ROCKER
BUTTON.

8 ON-ON, WITH OPAQUE, SINGLE-COLOR ROCKER BUTTON.

9 ON-OFF-ON, WITH OPAQUE, SINGLE-COLOR ROCKER BUTTON.

10 ON-OFF-(ON), WITH OPAQUE, SINGLE-COLOR ROCKER
BUTTON.

11 (ON)-OFF-(ON), WITH OPAQUE, SINGLE-COLOR ROCKER
BUTTON.

12  REFER TO QIP DIMENSIONAL REPORT

13 2002/95/EC/(RoHS) COMPLIANT

14 NOTE REMOVED.

X1X2 X3 X4 X5X6 ——— X7X8 X9 ——— X10X11X12X13X14

SWITCH TYPE: X1X2 = PR - POWER ROCKER

NOMINAL PANEL CUT OUT SIZE: X3 = E - 19.4X22.2 [.764x.874]

NUMBER OF POLES: X4 = D - DOUBLE

SWITCH FUNCTION: X5X6 = A1 - 
B1 - 
D1 - 
D3 - 
D4 - 
D5 - 

CURRENT RATING: X7X8 = 0Z - 


TERMINAL TYPE: X9 = E - FASTON™ TAB
L - SOLDER LUG

FRAME COLOR: X10 = B - BLACK
W - WHITE

ROCKER COLOR: X11 = B - BLACK
G - GREEN
R - RED
W - WHITE


SECONDARY ROCKER COLOR: X12 = Ø - NOT APPLICABLE
B - BLACK
G - GREEN
R - RED
W - WHITE

LEGEND TEXT PATTERN: X13 =



LEGEND TEXT COLOR: X14 = Ø - NOT APPLICABLE
G - GREEN
R - RED
B - BLACK
W - WHITE

OBSOLETE	1	PRED A1-07F-BB000	1634200-1
	1	PRED A1-07F-BB0BW	1634200-2
	1	PRED A1-07F-BB0CW	1634200-3
	1	PRED A1-07L-BB000	1634200-4
	1	PRED A1-07L-BB0BW	1634200-5
	1	PRED A1-07L-BB0CW	1634200-6
OBSOLETE	2	PRED B1-07F-BR000	1634200-7
	2	PRED B1-07L-BR000	1634200-8
	2	PRED B1-07F-BG000	1634200-9
OBSOLETE	2	PRED B1-07L-BG000	1-1634200-0
	3	PRED D1-07F-BB000	1-1634200-1
	3	PRED D1-07F-BB0DW	1-1634200-2
OBSOLETE	3	PRED D1-07F-BB0EW	1-1634200-3
	3	PRED D1-07L-BB000	1-1634200-4
	3	PRED D1-07L-BB0DW	1-1634200-5
OBSOLETE	3	PRED D1-07L-BB0EW	1-1634200-6
	4	PRED D3-07F-BB0FW	1-1634200-7
	4	PRED D3-07F-BB0GW	1-1634200-8
OBSOLETE	4	PRED D3-07L-BB0FW	1-1634200-9
	4	PRED D3-07L-BB0GW	2-1634200-0
	5	PRED D4-07F-BB000	2-1634200-1
OBSOLETE	5	PRED D4-07F-BB0FW	2-1634200-2
	5	PRED D4-07F-BB0GW	2-1634200-3
	6	PRED D5-07F-BB000	2-1634200-4
OBSOLETE	6	PRED D5-07F-BB0FW	2-1634200-5
	6	PRED D5-07F-BB0GW	2-1634200-6
	6	PRED D5-07F-BB0GW	2-1634200-6
	SHEET REF	ALCOSWITCH PART NUMBER.	TE PART NUMBER.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712	2-4-07	 TE Connectivity Ltd.	
DIMENSIONS: mm		CHK —	—		
		APVD —	—	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED	
		PRODUCT SPEC —	—		
MATERIAL —		FINISH —	—	SIZE A2	CAGE CODE 00779
		WEIGHT —	—	DRAWING NO C=1634200	RESTRICTED TO —
		CUSTOMER DRAWING	SCALE 3:1	SHEET 7 OF 7	REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PREDD4-07F-BB0FW](#)