

4

3


2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECR-21-112844	07SEP2021	RZ	WK

NOTES

- 1 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED
7. DURABILITY: 50 CYCLES



						Obsolete	
					1	1	BRASS 3 MALE CONTACT 4
					1	1	PHOS BRONZE 3 FEMALE CONTACT 3
					1	1	PE-606 INSULATOR 2
					1	1	ZINC ALLOY 4 BODY 1
					5--1	5--0	MATERIAL DESCRIPTION ITEM
					3	1	
QUANTITY PER ASSY						PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RITA ZUO 10 Mar 09		<div><div><div></div><div>TE</div></div>TE Connectivity</div>											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME											
		CHK ANSON MA 10 Mar 09		BNC ELBOW ADAPTOR PLUG – JACK 50 OHMS —											
		APVD BOB ZHAO 10 Mar 09													
		PRODUCT SPEC 108–112000													
		APPLICATION SPEC —													
MATERIAL SEE TABLE		FINISH —		SIZE A3		CAGE CODE 00779		DRAWING NO C–1634526		RESTRICTED TO —					
				WEIGHT 0.000000				CUSTOMER DRAWING		SCALE NTS		SHEET 1 OF 1		REV C2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1634526-1](#)