



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		F1	2-163680-2 MARKED OBSOLETE	04OCT2021	SCB	SS

D

C

B

A



NOTES:

- 1 PREFERRED HOLE SIZE: 0,8 (+0,1/-0,0) (.031) 0,9 (+0,1/-0,0) (.035) 1,0 (+0,1/-0,0) (.039) DEPENDING ON NUMBER OF POSITIONS OF CONNECTOR FOR MORE INFORMATION PLEASE CONTACT PRODUT-ENGINEERING DEPARTMENT.
- 2 ONLY FOR USE WITH G.M.T.S HEADERS
- 3 OBSOLETE

"L1" MAX.		"L" MAX		NUMBER OF LOADED POS.	ORDER NO.
mm	(inches)	mm	(inches)		
7,3	0,287	7,6	0,300	3	163680-1
9,8	0,386	10,1	0,398	4	163680-2
12,3	0,484	12,6	0,497	5	163680-3
14,8	0,582	15,1	0,595	6	163680-4
17,3	0,681	17,6	0,694	7	163680-5
19,8	0,779	20,1	0,792	8	163680-6
22,3	0,878	22,6	0,890	9	163680-7
24,3	0,976	25,1	0,989	1	163680-8
27,8	1,075	27,6	1,087	11	163680-9
29,8	1,173	30,1	1,186	12	1-163680-1
32,3	1,271	32,6	1,284	13	1-163680-2
34,8	1,370	35,1	1,382	14	1-163680-3
37,3	1,468	37,6	1,481	15	1-163680-4
39,8	1,567	40,1	1,579	16	1-163680-5
42,3	1,665	42,6	1,678	17	1-163680-6
44,8	1,764	45,1	1,776	18	1-163680-7
47,3	1,862	47,6	1,875	19	1-163680-8
49,8	1,960	50,1	1,973	20	1-163680-9
		52,6	2,071	21	2-163680-0
		55,1	2,170	22	2-163680-1
		57,6	2,268	23	2-163680-2
		60,1	2,367	24	2-163680-3

D

C

B

A

MATERIAL

HOUSING: GRAY CRASTIN SK643FR
RECEPTACLES: BRASS: TIN PLATED OVER NICKEL-BARRIER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm (INCHES)

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN 16-03-1973
CHK 19-03-1973
APVD -
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -
CUSTOMER DRAWING

16-03-1973
19-03-1973
-
-
-
-
-
-

16-03-1973
19-03-1973
-
-
-
-
-
-

TE Connectivity

FEMALE CONN.FOR COMMERCIAL INTERCONNECTION SYSTEM 2,5mm PITCH. TOP ENTRY

SIZE A2
CAGE CODE 00779
DRAWING NO C=163680

RESTRICTED TO -

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[163680-8](#)