





LOC	DIST	REVISIONS				DATE	DWN	APVD
		P	LTR	DESCRIPTION	ECO			
J	---		C		REVISED PER ECR-20-100815	01DEC2020	BDA	SW
			C1		REVISED PER ECR-21-102346	29APR2021	JP	VS



断面 "A" - "A"
(SECT.)



断面 "B" - "B"
(SECT.)

NOTES;

1. APPLICABLE HOUSING : CAP AND PLUG.
2. PRODUCT SPECIFICATION 108-5138
3. APPLICATION SPECIFICATION 114-5050
4. INSTRUCTION SHEET IS-105J
5. SELECTIVE GOLD PLATED AREA "C"
0.0004mm MIN THICK OVER Ni PLATE
ON INSIDE SURFACE

	錫めつき付・燐青銅 (PRE-TIN PHOS BR)	-4	-4
	金めつき・黄銅 (GOLD PLATE - BRASS) △5	-3	-3
170359, 170360 170363, 170364	錫めつき付・黄銅 (PRE-TIN BRASS)	170361-1	170365-1
嵌合相手型番 (MATING P/N)	材料・仕上 (MATERIAL - FINISH)	連鎖状端子型番 (STRIP P/N)	型番 (P/N)

WIRE RANGE
抱合電線断面積
0.12~0.35mm² (AWG #26~#22)

INSULATION DIA
被覆外径
1.2~1.75mm

MATERIAL 表参照
材料 (SEE TABLE) 0.2t

FINISH 表参照
仕上 (SEE TABLE)

DIMENSIONS
単位 概
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差

±0.4, ±1°0'

DWN 7. ymanoto 11, JUN. 98

CHK M. Shida 15 JUN 98

APVD M. Shida 15 JUN 98

PRODUCT SPEC
製品規格

注記参照
(SEE NOTES)



APPLICATION SPEC
取付適用規格

注記参照
(SEE NOTES)



WEIGHT

NAME
名称

ミニユニバーサルメイトンロックソケットコンタクトばら状端子
MINI UNIVERSAL MATE-N-LOK SOCKET CONTACT LOOSE PIECE

SIZE

CAGE CODE

DRAWING NO
番号

A4 00779 C-170365

SCALE
尺度

SHEET

1

OF

1

REV

C1

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170365-4](#)