



P	LTR	DESCRIPTION	DATE	DMN	APVD
H1	ADDED NEW DASH 5-4 PER NEW REQUEST	26APR2021	SH	SZ	



D




FOR 50 AND 130 POSITIONS ONLY

SECTION D-D
SCALE 8:1

C



B






A

NOTE:
1. MATERIAL:
HOUSING: LCP, UL 94V-0, BLACK COLOR.
CONTACTS: BRASS.
BOARDLOOKS: BRASS.
FINISH:
CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA,
3.81µm [150µ] MIN. MATE-TIN ON SOLDERTAIL, OVER
1.27µm [50µ] MIN. NICKEL, UNDERPLATED.
BOARDLOOKS: 3.81µm [150µ] MIN. TIN-CU OVER
1.27µm [50µ] MIN. UNDERPLATED.
3. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC.
G, J, H INDICATE NUMBER OF POSITION MARKED ON ASSEMBLY.
ALSO SEE TABLE.
GOLD FLASH OVER
0.762µm [30µ] MIN. PALLADIUM-NICKEL PLATED.

THIS DRAWING IS A CONTROLLED DOCUMENT.				REVISONS			
DMN F. YANG 31MAR2009		CHK S. CHIEN 31MAR2009		NAME PLUG ASSEMBLY, R/A, BTB, CHAMP .050, SERIES I		DATE 26APR2021	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A3 00779		RESTRICTED TO	
0 P/C 1 P/C 2 P/C 3 P/C 4 P/C		± ±0.25 ±0.2 ± ±		CAGE CODE C=1734099		SHEET 1 OF 5	
MATERIAL SEE NOTE		FINISH SEE NOTE		DRAWING NO 1734099		REV H1	
CUSTOMER DRAWING		TE Connectivity					

REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	AP'D
-	-	SEE SHEET 1	-	-	-



100	21	16	336	2.60	3.44	5-1734099-0
80	21	16	336	2.15	3.00	3-1734099-0
						1-1734099-0
						4-1734099-8
						2-1734099-8
						1734099-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DMN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

0 P/C

1 P/C

2 P/C

3 P/C

4 P/C

ANGLES

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±

±

±

±

±

±

±

MATERIAL

-

NAME

PLUG ASSEMBLY, R/A,

BTB, CHAMP .050, SERIES I

SIZE

A3

CAGE CODE

00779

DRAWING NO


1734099

RESTRICTED


NO

TE Connectivity



REVISIONS				
P	L/R	DESCRIPTION	DATE	DMN
-	-	SEE SHEET 1	-	-



FOR 50, AND 130
POSITIONS ONLY



FOR 40, 60, 68, 80, 100, 120, 140, 160, 180, AND 200
POSITIONS ONLY



THIS DRAWING IS A CONTROLLED DOCUMENT.		NAME		TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	
0 P/C ±-		1 P/C ±-		2 P/C ±-	
3 P/C ±-		4 P/C ±-		5 P/C ±-	
MATERIAL		FINISH		WEIGHT	
-		-		-	
CUSTOMER DRAWING		SIZE		CAGE CODE	
A3		00779		G=1734099	
SCALE		SHEET		REV	
-		3 of 5		H1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1734099-2](#)