






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-21-100237	22JAN2021	SK	DZ
	D2	REVISED PER ECR-21-125317	22DEC2021	PC	LC



LOCATION FOR
4~20 POSITION PARTS

- 1 MATERIAL: NYLON UL94V-0 COLOR: NATURAL
- 2 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY
- 3 ACCEPTS TE RECEPTACLE P/N'S 2110989-()
- 4 THESE HOUSINGS CAN ACCEPT OPTIONAL TPA(RETAINER),P/N ()-1969443-().
- 5 MATES WITH TE HEADER ASSEMBLIES:()-1744418-() & ()-1744439-().
- 6 PACKAGING: LOOSE PIECE
- 7 PER IEC 60335-1 SECT. 30, GWEPT 750C, NO FLAME or $T_e - T_i \leq 2S$

50.64	52.3	47.5	20	2-1744417-0
48.14	49.8	45.0	19	1-1744417-9
45.64	47.3	42.5	18	1-1744417-8
43.14	44.8	40.0	17	1-1744417-7
40.64	42.3	37.5	16	1-1744417-6
38.14	39.8	35.0	15	1-1744417-5
35.64	37.3	32.5	14	1-1744417-4
33.14	34.8	30.0	13	1-1744417-3
30.64	32.3	27.5	12	1-1744417-2
28.14	29.8	25.0	11	1-1744417-1
25.64	27.3	22.5	10	1-1744417-0
23.14	24.8	20.0	9	1744417-9
20.64	22.3	17.5	8	1744417-8
18.14	19.8	15.0	7	1744417-7
15.64	17.3	12.5	6	1744417-6
13.14	14.8	10.0	5	1744417-5
10.64	12.3	7.5	4	1744417-4
8.14	9.8	5.0	3	1744417-3
5.64	7.3	2.5	2	1744417-2
DIM C	DIM B	DIM A	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 23APR15		 TE Connectivity	
		CHK ASHWINI 23APR15			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD ASHWINI 23APR15		ECONOMY POWER 2.5 HOUSING GLOW WIRE -	
		PRODUCT SPEC 108-2418			
		APPLICATION SPEC 114-13315			
		WEIGHT -			
MATERIAL -		FINISH -		SIZE A2	CAGE CODE -
				DRAWING NO C-1744417	RESTRICTED TO -
Customer Drawing				SCALE N/A	SHEET 1 OF 1
				REV D2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1744417-3](#)