





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	—		C6	REVISED PER ECR-19-017851	26NOV2019	SM DZ
			D	REVISED PER ECR-19-017623	17DEC2020	MG DZ



1. APPLICABLE CONTACT PART NUMBER;
REC CONTACT: 175152-□ (#20-#16AWG)
175151-□ (#26-#22AWG)
2. TO BE USED WITH THE CONTACT WHICH IS RATED 105°C MAX
3. MATERIAL: PA66, UL94 V-0, GWIT 775°C

1-176282-5	130°C MAX	△3	GREEN 緑	2	1-176271-5
1-176282-1	130°C MAX	△3	NATURAL 自然色		1-176271-1△2
176282-□ 176292-□	105°C MAX	PA66	BLACK 黒		176271-9
			BLUE 青		176271-6
			YELLOW 黄		176271-4
			RED 赤		176271-2
MATING CONN. PART NUMBER 嵌合相手型番	TEMPERATURE RATING 定格温度	TYPE 種類	HOUSING COLOR 色	Pos. 極数	PART NUMBER 型番
	MATERIAL 材料				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.SHINDO 08NOV1989	TE Connectivity		
		CHK Y.FUJITA 08NOV1989			
		APVD Y.FUJITA 08NOV1989	NAME AMP UNIVERSAL POWER CONN. 3.96mm PITCH PLUG HOUSING 2 Pos. (SGL ROW) AMP ユニバーサルパワーコネクタ 2極 3.96mmピッチ キャップハウジング		
DIMENSIONS: mm		PRODUCT SPEC 108-5302			
		APPLICATION SPEC 114-5142			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C=176271
MATERIAL SEE TABLE		ANGLES FINISH ±3°	RESTRICTED TO —		
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
				REV D	

1. 適用端子型番;
リセコンタクト: 175152-□ (#20-#16AWG)
175151-□ (#26-#22AWG)
2. 適用コンタクトの使用温度は最大105°C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[176271-4](#)