





NUMBER C-176274

三角板 (3-d ANGLE PROJECTION)

METRIC

単位: 寸法 DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



- NOTES:
- PRODUCT SPEC.: 108-5302
 - APPLICABLE CONTACT P/N
REC CONTACT: 175152-□ (φ20-φ16AWG)
175151-□ (φ26-φ22AWG)
 - MATING CONN. P/N
CAP HSG: 176285-□ (FREE HANGING)
176295-□ (PANEL MOUNT)
TAB CONTACT: 175150-□ (φ20-φ16AWG)
175149-□ (φ26-φ22AWG)

- INSTRUCTION SHEET: IS-503J
- APPLICATION SPEC: 114-5142

- 注:
- 通用製品規格: 108-5302
 - 通用コンタクト型番
リセ・コンタクト: 175152-□ (φ20-φ16AWG)
175151-□ (φ26-φ22AWG)
 - 嵌合相手側製品型番
キャップ・ハウジング: 176285-□ (宙吊りタイプ)
176295-□ (パネル取付タイプ)
タブ・コンタクト: 175150-□ (φ20-φ16AWG)
175149-□ (φ26-φ22AWG)
 - 取扱説明書: IS-503J

							 TE Connectivity		
					組合電線断面積 (WIRE RANGE) — / — mm² (AWG —)		被覆外径 (INSULATION DIA.) — / — mmφ		
					材料 (MATERIAL) 6/6 ナイロン (UL94V-0) 6/6 NYLON (UL94V-0)		仕上 (FINISH) — / —		
					名称 (NAME) AMPユニバーサルパワーコネクタ 6極 3.96mmピッチ プラグハウジング (2列タイプ) AMP UNIVERSAL POWER CONN. 3.96mm PITCH PLUG HOUSING 6 Pos (2BL ROW)				
C	REVISED PER ECR-19-017623	M.G	D.Z	20AUG 2021	一般公差 10mm以下: ±0.2 10mm以上 30mm以下: ±0.25 30mm以上 100mm以下: ±0.3 角 度: ±3°		SIZE A3	LOC J	番号 (No.) C-176274
B1	REVISED PER ECO-11-005924	RK	HMR	08APR11	DR. M. SHINDO 89 11/8 DE. M. SHINDO 89 11/8 CHK. Y. FUJITA 89 11/8 APP. N. ONOUE 89 11/8		尺度 (SCALE)		REV. C
LTR	変更 (REVISION RECORD)	DR	CHK	DATE			SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[176274-2](#)