



D

C

B


A

CONNECTOR ASSEMBLY
EXAMPLARY LOADED



CONTACT DIMENSIONS


SCALE 5:1



CONTACT LAYOUT

	z	a	b	c	d	e	f
1	C	B	B	B	B	B	C
2	C	B	B	B	B	B	C
3	C	B	B	B	B	B	C
4	C	B	B	B	B	B	C
5	C	B	B	B	B	B	C
6	C	B	B	B	B	B	C
7	C	B	B	B	B	B	C
8	C	B	B	B	B	B	C
9	C	B	B	B	B	B	C
10	C	B	B	C	B	B	C
11	C	B	B	B	A	B	C
MULTI PURPOSE CENTER							
15	C	B	B	B	B	B	C
16	C	B	B	B	B	B	C
17	C	B	B	B	B	B	C
18	C	B	B	B	B	B	C
19	C	B	B	B	B	B	C
20	C	B	B	B	B	B	C
21	C	B	B	B	B	B	C
22	C	B	B	B	B	B	C
23	C	B	B	B	B	B	C
24	C	B	B	B	B	B	C
25	C	B	B	B	B	B	C

RECOMMENDED PCB-HOLE LAYOUT
COMPONENT SIDE SHOWN



PLATED THRU HOLES PARAMETERS

REFERENCE APPLICATION SPECIFICATION

	2	15	5	14	3-188834-0
OBSELETE	2	6	14		-1-188834-9
OBSELETE	2	5	14		-188834-9-
	2	4			188834-4
	2	3			188834-1
FINISH					PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B CARBO 13DEC05	TE Connectivity Ltd.	
DIMENSIONS: mm		CHK G SKIPPER 13DEC05	NAME MALE ASSEMBLY, Z-PACK 2mm HM, TYPE A	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-PLC ± 0.1 1-PLC ± 0.1 2-PLC ± 0.1 3-PLC ± 0.1 4-PLC ± 0.1 ANGLES ± 0.2		APVD G SKIPPER 13DEC05	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL 1		PRODUCT SPEC 108-19082	A100779C=188834	
FINISH SEE TABLE		APPLICATION SPEC 114-19029	WEIGHT 0	
		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 2 REV G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-188834-0](#)