



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECO-15-009269	25SEP2015	DD	LV
	D4	REVISED PER ECO-16-001206	28JAN2016	DD	LV

- 1 POLYESTER PBT, COLOR: SEE TABLE.
- 2 JACK HOUSING INTERFACE PER DIN 72594-1, ROAD VEHICLES - RADIO FREQUENCY INTERFACE - DIMENSIONS AND ELECTRICAL REQUIREMENTS.
- 3 PART HAS NOT BEEN TOOLED CONTACT TE.
- 4 PART HAS FEATURES FOR POWER INSERT IN POSITION 1.
- 5 DIMENSION APPLIES TO ALL CODING RIBS.




ISOMETRIC VIEW
SCALE 2:1





ISOMETRIC VIEW
WITH CLIP SLOT
SCALE 2:1

3	4	PER DETAIL BH	B	SIGNAL WHITE	7-1924855-2
	4	PER DETAIL AH	A	BLACK	7-1924855-1
3	4	PER DETAIL K	K	CURRY	6-1924855-0
		PER DETAIL G	G	BLUE GREY	5-1924855-7
3	3	PER DETAIL F	F	NUT BROWN	5-1924855-6
3	3	PER DETAIL E	E	LEAF GREEN	5-1924855-5
3	3	PER DETAIL D	D	CLARET VIOLET	5-1924855-4
		PER DETAIL C	C	SIGNAL BLUE	5-1924855-3
3	3	PER DETAIL B	B	SIGNAL WHITE	5-1924855-2
3	3	PER DETAIL A	A	BLACK	5-1924855-1
3	3	PER DETAIL K	K	CURRY	1-1924855-0
		PER DETAIL G	G	BLUE GREY	1924855-7
3	3	PER DETAIL F	F	NUT BROWN	1924855-6
3	3	PER DETAIL E	E	LEAF GREEN	1924855-5
		PER DETAIL D	D	CLARET VIOLET	1924855-4
3	3	PER DETAIL C	C	SIGNAL BLUE	1924855-3
		PER DETAIL B	B	SIGNAL WHITE	1924855-2
3	3	PER DETAIL A	A	BLACK	1924855-1
		KEYING	CODING REF	HOUSING COLOR	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. PETERSON CHK L. VARSIK APVD L. VARSIK	10DEC2008 10DEC2008 10DEC2008	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME JACK HOUSING, 2 POSITION, 8.0mm, FAKRA 4	
MATERIAL - 1		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		SIZE A200779	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2	REV D4




JACK HOUSING
WITHOUT CLIP SLOT




JACK HOUSING
WITH CLIP SLOT




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




DETAIL A
SCALE 3:1




DETAIL B
SCALE 3:1




DETAIL C
SCALE 3:1




DETAIL D
SCALE 3:1




DETAIL E
SCALE 3:1




DETAIL F
SCALE 3:1




DETAIL G
SCALE 3:1




DETAIL K
SCALE 3:1



DETAIL AH
SCALE 3:1



DETAIL BH
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. PETERSON CHK L. VARSIK APVD L. VARSIK		10DEC2008 10DEC2008 10DEC2008		 TE Connectivity							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME JACK HOUSING, 2 POSITION, 8.0mm, FAKRA 4							
mm				-									
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
MATERIAL				WEIGHT		A2		00779		C-1924855		-	
				CUSTOMER DRAWING		SCALE		4:1		SHEET		2 OF 2	
												REV D4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1924855-1](#)