





REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	A	REVISED PER ECO-18-007844	23MAY2018	RS	DR	
	B	REVISED PER ECO-18-013817	31AUG2018	RS	DR	
	C	REVISED PER ECO-19-009765	03JUL2019	RS	DR	




FOR 1958525-4 ONLY



FOR 1958525-1 ONLY




FOR 1958525-2 ONLY



FOR 1958525-3 ONLY

PRELIMINARY	100	LOOSE PIECE	60°	1958525-4
			90°	1958525-3
			45°	1958525-2
PRELIMINARY			30°	1958525-1
	QTY	PACKAGE TYPE	BEND ANGLE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI S 23MAY2018 CHK ROHDE DANIEL F 23MAY2018 APVD ROHDE DANIEL F 23MAY2018		 TE Connectivity Ltd.	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		PRODUCT SPEC 108-32046 APPLICATION SPEC 114-2162		TERMINAL, RING TONGUE, HEAT RESISTANT, STRATO-THERM 4 AWG, BENT	
MATERIAL		FINISH		SIZE	RESTRICTED TO
COPPER PER ASTM B-152 ANNEALED				CAGE CODE A2 00779	DRAWING NO C-1958525
CUSTOMER DRAWING				SCALE	REV
				4:1	1 OF 1 C

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE:

343°C[649°F]

VOLTAGE RATING:

NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
16.8–26.7mm² [33,100–52,600] CIR MILS
SOLID OR STRANDED

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1958525-3](#)