



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REVISED PER ECR-21-100237	22JAN2021	SK	DZ

D




2.80±0.15

2 POSITION



3 POSITION


4.60±0.10



4.80±0.15
4~20 POSITION

- 1 MATERIAL: NYLON UL94V-0
- 2 ACCEPTS TE RECEPTACLE
P/N'S 2110989-()
- 3 THESE HOUSINGS CAN ACCEPT
OPTIONAL TPA (RETAINER)
P/N 1969443-().
- 4 MATES WITH TE HEADER ASSEMBLIES
2132230-() & 2132415-().


C




0.75
TYP

0.75
TYP


DIM "A±0.20"



8.00




B



10.50

DIM "B±0.30"


LOCATION FOR
4~20 POSITION PARTS



ALTERNATE LOCATION FOR
2 AND 3 POSITION PARTS

NATURAL	50.64	52.3	47.5	20	2-1969442-0
	48.14	49.8	45.0	19	1-1969442-9
	45.64	47.3	42.5	18	1-1969442-8
	43.14	44.8	40.0	17	1-1969442-7
	40.64	42.3	37.5	16	1-1969442-6
	38.14	39.8	35.0	15	1-1969442-5
	35.64	37.3	32.5	14	1-1969442-4
	33.14	34.8	30.0	13	1-1969442-3
	30.64	32.3	27.5	12	1-1969442-2
	28.14	29.8	25.0	11	1-1969442-1
	25.64	27.3	22.5	10	1-1969442-0
	23.14	24.8	20.0	9	1969442-9
	20.64	22.3	17.5	8	1969442-8
	18.14	19.8	15.0	7	1969442-7
	15.64	17.3	12.5	6	1969442-6
COLOR	13.14	14.8	10.0	5	1969442-5
	10.64	12.3	7.5	4	1969442-4
	8.14	9.8	5.0	3	1969442-3
	5.64	7.3	2.5	2	1969442-2
	DIM C	DIM B	DIM A	NO. OF POSITIONS	PART NUMBER

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 09SEP2016	TE Connectivity		
DIMENSIONS:		CHK TOM MICHIELUTTI 27FEB14			
mm		APVD TOM MICHIELUTTI 27FEB14	NAME ECONOMY POWER 2.5 TPA HOUSING		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	-		
0 PLC ±-		108-2418	-		
1 PLC ±0.50		APPLICATION SPEC	-		
2 PLC ±0.25		114-13315	-		
3 PLC ±-		WEIGHT	-		
4 PLC ±-		Customer Drawing	-		
ANGLES ±-		SCALE	N/A		
FINISH		SHEET	1 OF 1		
-		REV	C1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1969442-8](#)