

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	PRODUCTION ISSUE	18JAN2019	PNT	MT

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

TABLE OF DIMENSIONS

THIS DRAWING IS UNPUBLISHED: TE Connectivity Ltd.	PART NUMBER	H		J			P ±10%	R Ref	S Ref	T		U ±10%	JO ±10%	HW ±20%	JW ±20%							
		Min	Max	Min -3,-4, -25	Min -12, -100	Max				Ref	Ref											
		a	b	a	a	b	b	b	b	b	b	b	b	b	b							
	202D921	19.3 [.76]	13.0 [.51]	6.3 [.25]	4.5 [.18]	2.1 [.08]	60.2 [2.37]	11.7 [.46]	3.0 [.12]	1.0 [.04]	15.7 [.62]	37.6 [1.48]	1.5 [.06]	1.14 [.045]								
© COPYRIGHT -	202D932	26.1 [1.03]	19.1 [.75]	7.6 [.30]	5.5 [.22]	2.6 [.10]	74.2 [2.92]	12.2 [.48]	3.0 [.12]	1.0 [.04]	20.3 [.80]	45.0 [1.77]	1.8 [.07]	1.14 [.045]								
	202D953	34.2 [1.35]	26.0 [1.02]	9.6 [.38]	6.6 [.26]	3.1 [.12]	84.3 [3.32]	12.2 [.48]	3.0 [.12]	1.0 [.04]	20.9 [.90]	51.1 [2.01]	1.8 [.07]	1.14 [.045]								
	202D963	43.6 [1.72]	34.1 [1.34]	11.4 [.45]	7.8 [.31]	3.6 [.14]	99.6 [3.92]	12.2 [.48]	3.0 [.12]	1.65 [.065]	26.2 [1.03]	57.7 [2.27]	1.8 [.07]	1.14 [.045]								
DIMENSIONS:		DWN PRAVEEN N T 18JAN2019				MATERIAL SEE SHEET 2			FINISH			—										
mm [INCHES]		CHK N NAGAR 18JAN2019				 TE Connectivity Ltd.																
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M TAYLOR 18JAN2019				NAME BOOT, STRAIGHT																
		PRODUCT SPEC —				SIZE CAGE CODE DRAWING NO																
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	± — ± — ± — ± — ± — ± —	APPLICATION SPEC —				A4 00779 C—202D921-XX-0THRU963-XX-0																
		WEIGHT —				—																
		CUSTOMER DRAWING				SCALE DNS		SHEET 1 OF 2		REV U												

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATABILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42; /86; /180	S1017; S1048; S1030
-4	Polyolefin, Flexible	RT-1304	/42; /86; /180	S1017; S1048; S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42; /86; /225	S1017; S1048; S1206
-100	Polyolefin, Semi-flexible ZEROHAL	RW-2082	/86; /180	S1048; S1030

ORDERING INFORMATION

202D9XX -XX -XX /XX -0

Base part number

Material dash number
(See Compatability Chart)

Modification number

Adhesive slash number
(If necessary, see Compatability Chart)

Color Designator

NOTES

- Dimensions appearing in table are as follows:
 - As Supplied
 - After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
- Molding port is optional. When -00 modification number is specified molding port will be located as shown.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T CHK N NAGAR APVD M TAYLOR	18JAN2019 18JAN2019 18JAN2019	MATERIAL —	FINISH —		
				TE Connectivity Ltd.		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC —	NAME BOOT, STRAIGHT	—			
			APPLICATION SPEC —	SIZE A4	CAGE CODE 00779	DRAWING NO 202D921-XX-0THRU963-XX-0
WEIGHT	CUSTOMER DRAWING					
						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202D932-3-00-0](#)