



REVISIONS

a) Part as supplied.



b) Part after unrestricted recovery.



(See note 2 regarding eyelet feature)

DIMENSIONS in millimetres
[in inches, for reference]

② See over for explanation of Notes

Part No.	H		J		P	R	S	T	U&V	JO	HW	JW	X	Y
	Min a	Max b	Min a	Max b										
① 202K121	24 [.94]	1.4 [.41]	12 [.47]	5.6 [.22]	38 [1.50]	21 [.83]	3.0 [.12]	1.0 [.04]	12 [.47]	8.5 [.33]	1.6 [.06]	0.9 [.04]	24 [.94]	13 [.51]
① 202K132	30 [1.18]	14.2 [.56]	14 [.55]	5.9 [.23]	55 [2.17]	32 [1.26]	3.0 [.12]	1.0 [.04]	12 [.47]	11.5 [.45]	1.8 [.07]	1.0 [.04]	24 [.94]	18 [.71]
① 202K142	31 [1.22]	18.0 [.71]	15 [.59]	7.1 [.28]	67 [2.64]	35 [1.38]	3.0 [.12]	1.0 [.04]	20 [.79]	17.0 [.67]	1.8 [.07]	1.0 [.04]	32 [1.26]	25 [.98]
① 202K153	36 [1.42]	22.4 [.88]	18 [.71]	8.4 [.33]	80 [3.15]	42 [1.65]	3.0 [.12]	1.0 [.04]	20 [.79]	19.5 [.77]	2.0 [.08]	1.0 [.04]	32 [1.26]	30 [1.18]
202K163	42 [1.65]	28.2 [1.11]	21 [.83]	9.9 [.39]	99 [3.90]	61 [2.40]	3.0 [.12]	1.7 [.07]	20 [.79]	21.0 [.83]	2.2 [.09]	1.0 [.04]	52 [2.05]	30 [1.18]
202K174	60 [2.36]	35.1 [1.38]	35 [1.38]	15.7 [.62]	130 [5.12]	72 [2.83]	3.0 [.12]	1.7 [.07]	20 [.79]	39.0 [1.54]	3.2 [.13]	1.5 [.06]	52 [2.05]	50 [1.97]
202K185	66 [2.60]	44.5 [1.75]	38 [1.50]	16.8 [.66]	170 [6.69]	90 [3.54]	3.0 [.12]	2.0 [.08]	20 [.79]	51.5 [2.03]	3.8 [.15]	2.0 [.08]	52 [2.05]	70 [2.76]

DIMENSIONS:

mm [INCHES]

DWN

PRAVEEN N T

18JAN2019

MATERIAL

SEE SHEET 2

FINISH

-

CHK

N NAGAR

18JAN2019

APVD

M TAYLOR

18JAN2019

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

NAME

BOOT, STRAIGHT WITH LIP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-202K1XX-12-0

-

CUSTOMER DRAWING


SCALE

DNS

SHEET

1 OF 2

REV 5



THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

TE CONNECTIVITY LTD.

COPYRIGHT -

©

0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

(COMPATIBILITY CHART)

Material Dash Number	Material Description	SPEC Number	Coating Slash NO	Coating S NO
—12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A

(Ordering Information)

202K1XX-XX-0



NOTES


- ① Dimension U does not apply on sizes 202K121 thru 202K153.
- ② Part is supplied without eyelet feature as standard
If eyelet feature is required, add CS-1863 to description:—
202K132-12-CS-1836-0
If eyelet feature and clip is required, add CS-1858 to description:—
202K132-12-CS-1858-0
- ③ 202K121-12-00-0 potting port X is at 90° to potting port Y.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE CONNECTIVITY LTD.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	18JAN2019	MATERIAL —	FINISH —
	CHK N NAGAR	18JAN2019	 TE Connectivity Ltd.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M TAYLOR	18JAN2019		
	PRODUCT SPEC —		SIZE A4	
	APPLICATION SPEC —		CAGE CODE 00779	DRAWING NO C-202K1XX-12-0
	WEIGHT —		RESTRICTED TO —	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	CUSTOMER DRAWING		SCALE DNS	SHEET 2 of 2
		REV 5		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202K121-12-0](#)