






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECO-20-017853: G-CONTACT TAIL GOLD FLASH	18DEC2020	A.L	H.L
	B1	REVISED PER ECO-16-009003	14JUN16	B.J	S.Y


リール引出し方向
DIRECTION OFF TOP OF REEL



SEE DETAIL F

カバートープ
リッター部
外周一巻
WEEDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN
A TURN.

CONNECTOR DETAIL




NO	950	59.5	57.7	57.1	54.5	95	61.8	62.1	88	84.4	42.25	220	BLACK	△3-2040714-7
NO	950	59.5	57.7	57.1	54.5	95	61.8	62.1	88	84.4	42.25	220	BLACK	△3-2040714-6
SEALANT	QTY	T	S	P	N	W	E	D	C	B	A	POS.	HSG COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 純
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差



MATERIAL
材料

FINISH
仕上

0	PLC	± 0.3
1	PLC	± 0.3
2	PLC	± 0.3
3	PLC	± 0.3
4	PLC	± 0.3
ANGLES		± 3°

DWN Y.NAKAZAWA 12MAR2008

CHK T.FUTATSUGI 12MAR2008

APVD T.FUTATSUGI 12MAR2008

PRODUCT SPEC

製品規格

108-5560

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

A
FH 0.5BTB CONNECTOR 220 POS
REC 4H WITH G-CONT. AND CAP

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C=2040714	

SCALE 尺度	1:1	SHEET 1 OF 3	REV C
-------------	-----	-----------------	----------

4

3






2

1

© 2008 TE Connectivity. All Rights Reserved.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

G-G
(GROUND POSITION)
(SCALE 8:1)H-H
(SIGNAL POSITION)
(SCALE 8:1)

- 1 MATERIAL; HOUSING: HIGH TEMP THERMO PLASTIC UL94V-0
CONTACT: COPPER ALLOY
SOLDER PEG: COPPER ALLOY
- 2 FINISH ; SIGNAL CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.00076mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.
GROUND CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.00076mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.
SOLDER PEG: 0.001mm MIN TIN PL. OVER
0.0013mm MIN Ni PL ALL OVER.
- 3 THIS POSITION IS GROUND CIRCUIT.
- 4 FINISH ; SIGNAL CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.
GROUND CONTACT: UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002mm MIN Au PL.
SOLDERING AREA 0.00005mm MIN Au PL.
SOLDER PEG: 0.001mm MIN TIN PL. OVER
0.0013mm MIN Ni PL ALL OVER.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位: 毫米MATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差0 PLC ± 0.3
1 PLC ± 0.3
2 PLC ± 0.3
3 PLC ± 0.3
4 PLC ± 0.3
ANGLES ± 3°FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING



TE Connectivity Ltd.

NAME
名称

EMBOSS ASSY

FH 0.5BTB CONNECTOR 220 POS
REC 4H WITH G-CONT. AND CAP

SIZE

A3

CAGE CODE

00779

DRAWING NO
番号

C=2040714

RESTRICTED TO

SCALE
尺度 4:1


SHEET

2 OF 3



REV
C

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



REFERENCE P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity Ltd.			
		CHK					
DIMENSIONS: 單位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称 EMOSS ASSY FH 0.5BTB CONNECTOR 220 POS REC 4H WITH G-CONT. AND CAP			
		0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°					
MATERIAL 材料		FINISH 仕上				SIZE A3	
		WEIGHT				CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO 番号 C=2040714			
				RESTRICTED 番号 —			
				SCALE 尺度 4:1			
				SHEET 3 OF 3			
				REV C			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2040714-6](#)