





1. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2. WILL ACCEPT SEVEN (7) TYPE XII SOCKET CONTACTS.
3. #4 FASTENER RECOMMENDED FOR MOUNTING.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
5. TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

4-40 THREADED INSERTS	NO	A	206227-6
3.81±0.08 [.150±.003]	YES	A	206227-5
3.81±0.08 [.150±.003]	NO	B	206227-2
3.81±0.08 [.150±.003]	NO	A	206227-1
C	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.HARDY 05/31/94	TE Connectivity			
DIMENSIONS: mm[INCHES]		CHK W.G.LENKER 06/08/94	NAME			
		APVD A.FRANTUM 07/13/94	PRODUCT SPEC			
		108-10024				
		APPLICATION SPEC				
MATERIAL NYLON, BLACK	FINISH -	WEIGHT -	SIZE A1	CAGE CODE 00779	DRAWING NO 206227	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV N	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206227-6](#)