

D

C

B

A




D

C



B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
U		REVISED PER ECO-21-006945	28OCT2021	RK	MZ



DETAIL A



DETAIL B

- WILL ACCEPT (20) MULTIMATE AND 2 TYPE XII PIN CONTACTS.
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- NUMBER 4 FASTENERS RECOMMENDED FOR MOUNTING.

HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.

APPLIES TO 206613-6 ONLY.





PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY INDENTIFICATION.

HOUSING: NYLON, RED.
PERIPHERAL SEAL: ELASTOMER, BLACK.

WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE

OBSOLETE	8/4	Ø3.81±0.08(.125±.003) HOLES	YES	A	1-206613-2
	4	#4-40 THREADED INSERTS	NO	A	1-206613-0
OBSOLETE	4	Ø3.81±0.08(.125±.003) HOLES	YES	A	206613-9
PRELIMINARY	6/4	Ø3.81±0.08(.125±.003) HOLES	YES	A	206613-7
OBSOLETE	4	#4-40 THREADED INSERTS	NO	A	206613-6
	4	Ø3.81±0.08(.125±.003) HOLES	YES	A	206613-5
	4	Ø3.81±0.08(.125±.003) HOLES	NO	B	206613-3
	4	Ø3.81±0.08(.125±.003) HOLES	NO	A	206613-1
NOTES		MOUNTING FEATURE	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 05/26/94	 TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK R.STONE 6-23-94			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-10024	RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC -		
MATERIAL 	FINISH -	WEIGHT -	A1 00779  206613		
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV U	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206613-1](#)