




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S	REVISED PER ECO 20-015430	5-25-21	CT	RL



1. MATERIAL & FINISH YELLOW CHROMATE
SHELL: DIE CAST ALUM. ALLOY PER QQ-A-591 OR
OR ASTM B211, 6061-T6/6511 OR ASTM B209
2024-T4/T351
FINISH: CAD. PLATED PER QQ-P-416, TYPE I, CLASS 2
YELLOW CHROMATE CONVERSION.
INSULATOR, HARD: EPOXY PER MIL-M-24325.
INSULATOR, SOFT: FLUOROSILICONE RUBBER, COLOR: BLUE.
GROMMET PROTECTOR: ALUM. ALLOY, FINISH: BLUE EPOXY.
POLARIZING POST & NUTS: STAINLESS STEEL.
MALE JACKSCREW: STAINLESS STEEL.
SCREWS & WASHERS: STEEL, CAD. PLATED PER QQ-P-416.
DUST CAP: CLEAR VINYL.

"B"				"C"				"D"			
22	20	16	12	22	20	16	12	22	20	16	12
.736	.827	.782	.793	.797	.893	.893	.893	.737	.700	.824	.824
[18.69]	[21.00]	[19.86]	[20.14]	[20.24]	[22.68]	[22.68]	[22.68]	[18.72]	[17.78]	[20.93]	[20.93]
.688	.769	.735	.746	.769	.865	.865	.865	.688	.585	.746	.746
[17.48]	[19.53]	[18.67]	[18.95]	[19.53]	[21.97]	[21.97]	[21.97]	[17.48]	[14.86]	[18.95]	[18.95]

- △ CONTACTS SHOWN IN POSITION FOR ILLUSTRATION ONLY, ARE INCLUDED IN A CONTAINER WITHIN CONNECTOR PACKAGE FOR SHIPMENT, EXCEPT P/N'S 1-207596-1 THRU 2-207596-0.

4. COAX CONTACTS & SEALING BOOTS MUST BE ORDERED SEPARATELY.

- 5 FOR CONTACT SIZE 22 DIMENSION "B" REPRESENTS PIN CONTACTS & DIMENSION "D" REPRESENTS SOCKET CONTACTS.


- 6 ALL METRIC DIMENSIONS ARE SHOWN IN PARENTHESIS.

7. FOR MATING CONNECTOR SEE 207595.

- CONNECTORS ORDERED LESS CONTACTS WILL BE MARKED WITH SAME P/N AS CONNECTORS ORDERED WITH CONTACTS.

	INSERT ARRANGEMENT			
	26	32C2	67	106
"A" MAX	1.541 [39.14]	1.625 [41.28]	1.425 [36.20]	1.541 [39.14]

PART NO.		ARRANGEMENT		PART NO. (LESS CONTACTS) 	
		IN MODULE "A"	IN MODULE "B"		
	207596-1	(106S)	(67P)	1-207596-1	OBsolete
OBsolete	207596-2	(106S)	(26P)	1-207596-2	OBsolete
OBsolete	207596-3	(106S)	(106S)	1-207596-3	OBsolete
OBsolete	207596-4	(106S)	(106P)	1-207596-4	OBsolete
	207596-5	(106P)	(106P)	1-207596-5	OBsolete
OBsolete	207596-6	(106P)	(26S)	1-207596-6	OBsolete
OBsolete	207596-7	(106P)	(67S)	1-207596-7	OBsolete
OBsolete	207596-8	(106P)	(67P)	1-207596-8	OBsolete
	207596-9	(106P)	(32C2S)	1-207596-9	OBsolete
	1-207596-0	(106S)	(32C2P)	2-207596-0	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG 23-SEP-03 J. KAISER CHK 23-SEP-03 J. MARKEY APD 23-SEP-03 J. MARKEY	 TE Connectivity
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO	
	0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± .005[0.13] 4 PLC ± . ANGLES ± .	PLUG CONNECTOR INSTALLATION (WITH CENTER MALE JACKSCREW)	RESTRICTED TO
MATERIAL -	FINISH -	WEIGHT 0.000000	A1 00779 C-207596 —
		CUSTOMER DRAWING	SCALE 3:1 SHEET 1 of 1 REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[207596-1](#)