


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	AS PER ECO-20-015929	10NOV2020	RJ	MT

a) Part as supplied.



b) Part after unrestricted recovery.




TABLE OF DIMENSIONS

PART NUMBER	H	J		J0	K	M	P	R	U	T	JW	Hole DIA	Torque Nm
	Ref b	Min a	Max b	Max b	Ref b	THREAD b	±10% b	±10% b	±10% b	Ref b	±20% b	±0.5 [0.02]	
207W213-01	12.0 [.47]	10.0 [.39]	4.0 [.15]	15.3 [.60]	23.0 [.90]	20.0 [.78]	62.0 [2.44]	49.0 [1.93]	10.0 [.39]	32.0 [1.25]	1.0 [.04]	24.0 [.94]	3
207W223-01	20.0 [.78]	18.0 [.71]	7.0 [.27]	19.5 [.76]	33.0 [1.30]	30.0 [1.18]	72.0 [2.83]	59.0 [2.32]	10.0 [.39]	42.0 [1.65]	1.8 [.07]	34.0 [1.33]	8
207W234-01	31.0 [1.22]	28.0 [1.10]	12.0 [.47]	27.0 [1.06]	46.0 [1.81]	42.0 [1.65]	87.0 [3.42]	74.0 [2.91]	10.0 [.39]	58.0 [2.28]	2.5 [.10]	47.0 [1.85]	11
207W245-01	45.0 [1.77]	42.0 [1.65]	18.0 [.71]	32.2 [1.26]	59.5 [2.34]	56.0 [2.20]	102.0 [4.01]	89.0 [3.50]	10.0 [.39]	71.0 [2.79]	3.0 [.12]	60.5 [2.38]	14
207W256-01	68.0 [2.67]	64.0 [2.52]	30.0 [1.18]	39.0 [1.53]	84.0 [3.30]	80.0 [3.15]	122.0 [4.80]	109.0 [4.29]	10.0 [.39]	97.0 [3.82]	3.0 [.12]	85.0 [3.34]	16
207W264-01	40.0 [1.57]	38.0 [1.49]	15.0 [.59]	28.3 [1.11]	54.0 [2.12]	50.0 [1.97]	95.0 [3.74]	82.0 [3.22]	10.0 [.39]	66.5 [2.62]	2.5 [.10]	55.0 [2.16]	11

TE Connectivity. All Rights Reserved.




DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.50[.10]
2 PLC	± 0.25[.01]
3 PLC	± 0.13[.005]
4 PLC	± -
ANGLES	± 1°



DWN

PRAVEEN N T

CHK

N NAGAR

APVD

M TAYLOR

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

MATERIAL

SEE SHEET 2

FINISH

—



TE Connectivity Ltd.

NAME

FEEDTHROUGH, SEAL

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-

207W213-XX-01-0THRU264-XX-01-0

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 of 2

REV G1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	SPEC REFERENCE	COATING SLASH NUMBER	COATING S NUMBER
-3	POLYOLEFIN, SEMI RIGID	RT-301	/42; /86; /180	S1017; S1048; S1030
-4	POLYOLEFIN, FLEXIBLE	RT-1304	/42; /86; /180	S1017; S1048; S1030
-25	ELASTOMER, FLUID RESISTANT	RW-2070	/42; /86; /225	S1017; S1048; S1206
-100	POLYOLEFIN, SEMI FLEXIBLE, ZEROHAL	RW-2082	/86; /180	S1048; S1030

ORDERING INFORMATION

BASE PART NUMBER _____
 MATERIAL DASH NUMBER _____
 MODIFICATION NUMBER _____
 ADHESIVE SLASH NUMBER _____
 (SEE COMPATIBILITY CHART BELOW)
 COLOR DESIGNATOR _____

207W2XX -XX XX /XX -0

NOTES


- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
 - AS SUPPLIED
 - AFTER UNRESTRICTED RECOVERY
- COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY 1.5mm[.06] MAX.
- RECOMENDED MAXIMUM PANEL THICKNESS IS 10mm[.393].

TE Connectivity. All Rights Reserved.

—



DIMENSIONS: mm [INCHES]		DWN PRAVEEN N T	25JAN2019	MATERIAL —		FINISH —		
		CHK N NAGAR	25JAN2019	TE Connectivity Ltd.				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.50[.10] 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES ± 1°		APVD M TAYLOR	25JAN2019					NAME FEEDTHROUGH, SEAL —
		PRODUCT SPEC —						
		APPLICATION SPEC —		SIZE A4		CAGE CODE 00779	DRAWING NO C-207W213-XX-01-0THRU264-XX-01-0	RESTRICTED TO —
		WEIGHT						
CUSTOMER DRAWING				SCALE DNS	SHEET 2 of 2	REV G1		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[207W256-3-01/42-0](#)