








- 1 THIS PLUG WILL ACCEPT 2 TYPE I, SIZE 12 PIN CONTACTS AND 8 MULTIMATE PIN CONTACTS
- 2 MAXIMUM WIRE INSULATION ACCEPTED BY THIS PLUG IS $\varnothing 2.67$ [$\varnothing 0.105$] FOR MULTIMATE PIN CONTACTS

-  3 WHITE STRIPE INDICATES MAJOR KEYWAY
-  4 WHITE DOT INDICATES MAJOR KEYWAY
-  5 TE LOGO LOCATED ANYWHERE ON THIS SURFACE

OBSOLETE		213130-3
		213130-2
	-	213130-1
KEYWAY MARKING		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 11/03/89	 TE Connectivity Ltd.			
DIMENSIONS: mm [INCHES]		CHK R.STONE 11-8-89				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.KAPEZYNSKI 11-8-89	NAME		
	0 PLC ± -		PRODUCT SPEC	PLUG, CPC, ARRANGEMENT 17-10M, REVERSE SEX, SERIES 4, CLASS A		
	1 PLC ± -		APPLICATION SPEC			
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO
UL 94V-0 RATED, NYLON BLACK		-	-	A2	00779	C-213130
CUSTOMER DRAWING			SCALE	4:1	SHEET	1 OF 1
			REV	C		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[213130-1](#)