



P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	LC20-0097-18 / ECO-18-014539	08OCT2018	DM	BJ
	F	LC20-0036-19 / ECO-19-005225	18APR2019	DM	BJ
	G	LC20-0074-19 / ECO-19-010038	09AUG2019	DM	BJ
	H	LC20-0091-20 / ECO-20-012656	08SEP2020	DM	BJ



A/R	A/R	A/R	A/R	METAL SEALANT	7
I	I	I	I	INSTALLATION INSTRUCTION SHEET, 408-32203	6
I	I	I	I	ABRASIVE TAPE	5
2	2	2	2	MULTI SHEAR HEAD BOLT, M14 SIZE, ALUMINUM ALLOY	4
A/R	A/R	A/R	A/R	INHIBITOR	3
I	-	-	-	EXPOSED LENGTH (64 [2.5])	2
-	I	-	-	EXPOSED LENGTH (229 [9])	
-	-	I	-	EXPOSED LENGTH (152 [6])	
-	-	-	I	EXPOSED LENGTH (305 [12])	
I	I	I	I	CONNECTOR SLEEVE BODY, ALUMINUM ALLOY, TIN PLATED	1
-4	-3	-2	-1	DESCRIPTION	ITEM NO
QTY				PARTS LIST	



1. ACCOMMODATES:
2 SOL - 4/0 STR.
2. MARKING:
- STE**
- [CATALOG NO]
2 SOL-4/0 STR
MADE IN [COUNTRY OF ORIGIN]
[DATE CODE]
- (SEE TABLE FOR CATALOG NO MARKING)
3. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
4. CONNECTOR CONTAINS FACTORY APPLIED
ANTI-OXIDE INHIBITOR.
5. FINISH:
CU STUD AND AL CONNECTOR BODY
ELECTRO-TIN PLATED.
6. INSTALL BOLTS WITH 13 mm [1/2 inch]
HEX SOCKET.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09 JAN 2015 CHK D. MURUGIAH A BULZA 16 MAY 2016 APVD 25 MAY 2016 B. JOHNSON		 TE Connectivity	
DIMENSIONS: mm [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SHEARBOLT PIN CONNECTOR, TIN PLATED, 2/0 AWG CU STUD TO 2-4/0 AWG CONDUCTORS	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH			
MATERIAL SEE BOM		SEE BOM		PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	
				SIZE A2	CAGE CODE 00779
				DRAWING NO C=2182442	
				RESTRICTED TO -	
				SCALE NTS	SHEET OF 1
				REV H	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2182442-2](#)