


8 DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 105°C RATED, COPPER 16/30 STRANDED.
PER UL STYLE AWM 1015.


9 PRELIMINARY.

10 FOR PART NUMBER 5-2213362-4 ONLY,
STRIP AND REMOVE INSULATION AS SHOWN.
LEAD WIRES TO BE SOLDER DIPPED.

11. MUST BE USED WITH EITHER GASKET P/N 2213469-1
OR P/N 2324246-1 (SOLD SEPARATELY).



1471-9 (3/11)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2213362-3](#)