










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



ASSEMBLED VIEW



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 08FEB2016	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 08FEB2016			
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		ANTI-VANDAL SWITCH 19mm MOVING RING LED		
	FINISH		RESTRICTED TO		
MATERIAL	-	WEIGHT	-	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		APVD HILL RYAN 08FEB2016	DRAWING NO C=2213767		REV B1
		SCALE 1:1		SHEET 2 OF 4	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SINGLE POLE- LOCKING	GOLD	BLUE	24V	AV1911E724R04	4-2213767-0
	SILVER	BLUE	24V	AV1911E724Q04	3-2213767-9
	GOLD	BLUE	12V	AV1911E712R04	3-2213767-8
	SILVER	BLUE	12V	AV1911E712Q04	3-2213767-7
	GOLD	GREEN	24V	AV1911E624R04	3-2213767-6
	SILVER	GREEN	24V	AV1911E624Q04	3-2213767-5
	GOLD	GREEN	12V	AV1911E612R04	3-2213767-4
	SILVER	GREEN	12V	AV1911E612Q04	3-2213767-3
	GOLD	YELLOW	24V	AV1911E524R04	3-2213767-2
	SILVER	YELLOW	24V	AV1911E524Q04	3-2213767-1
	GOLD	YELLOW	12V	AV1911E512R04	3-2213767-0
	SILVER	YELLOW	12V	AV1911E512Q04	2-2213767-9
	GOLD	RED	24V	AV1911E324R04	2-2213767-8
	SILVER	RED	24V	AV1911E324Q04	2-2213767-7
	GOLD	RED	12V	AV1911E312R04	2-2213767-6
	SILVER	RED	12V	AV1911E312Q04	2-2213767-5
	GOLD	WHITE	24V	AV1911E124R04	2-2213767-4
	SILVER	WHITE	24V	AV1911E124Q04	2-2213767-3
	GOLD	WHITE	12V	AV1911E112R04	2-2213767-2
	SILVER	WHITE	12V	AV1911E112Q04	2-2213767-1
SINGLE POLE- MOMENTARY	GOLD	BLUE	24V	AV1910E724R04	2-2213767-0
	SILVER	BLUE	24V	AV1910E724Q04	1-2213767-9
	GOLD	BLUE	12V	AV1910E712R04	1-2213767-8
	SILVER	BLUE	12V	AV1910E712Q04	1-2213767-7
	GOLD	GREEN	24V	AV1910E624R04	1-2213767-6
	SILVER	GREEN	24V	AV1910E624Q04	1-2213767-5
	GOLD	GREEN	12V	AV1910E612R04	1-2213767-4
	SILVER	GREEN	12V	AV1910E612Q04	1-2213767-3
	GOLD	YELLOW	24V	AV1910E524R04	1-2213767-2
	SILVER	YELLOW	24V	AV1910E524Q04	1-2213767-1
	GOLD	YELLOW	12V	AV1910E512R04	1-2213767-0
	SILVER	YELLOW	12V	AV1910E512Q04	2213767-9
	GOLD	RED	24V	AV1910E324R04	2213767-8
	SILVER	RED	24V	AV1910E324Q04	2213767-7
	GOLD	RED	12V	AV1910E312R04	2213767-6
	SILVER	RED	12V	AV1910E312Q04	2213767-5
	GOLD	WHITE	24V	AV1910E124R04	2213767-4
	SILVER	WHITE	24V	AV1910E124Q04	2213767-3
	GOLD	WHITE	12V	AV1910E112R04	2213767-2
	SILVER	WHITE	12V	AV1910E112Q04	2213767-1
POLE/THROW	CONTACT	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PN	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08FEB2016 NAGALAKSHMI K CHK 08FEB2016 HILL RYAN APVD 08FEB2016 HILL RYAN PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ANTI-VANDAL SWITCH 19mm MOVING RING LED	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL -		FINISH -		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=2213767	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1	
				SHEET 3 of 4	
				REV B1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

DOUBLE POLE-LOCKING

DOUBLE POLE-MOMENTARY

POLE/THROW

GOLD	BLUE	24V	AV1921E724R04	8-2213767-0	
SILVER	BLUE	24V	AV1921E724Q04	7-2213767-9	
GOLD	BLUE	12V	AV1921E712R04	7-2213767-8	
SILVER	BLUE	12V	AV1921E712Q04	7-2213767-7	
GOLD	GREEN	24V	AV1921E624R04	7-2213767-6	
SILVER	GREEN	24V	AV1921E624Q04	7-2213767-5	
GOLD	GREEN	12V	AV1921E612R04	7-2213767-4	
SILVER	GREEN	12V	AV1921E612Q04	7-2213767-3	
GOLD	YELLOW	24V	AV1921E524R04	7-2213767-2	
SILVER	YELLOW	24V	AV1921E524Q04	7-2213767-1	
GOLD	YELLOW	12V	AV1921E512R04	7-2213767-0	
SILVER	YELLOW	12V	AV1921E512Q04	6-2213767-9	
GOLD	RED	24V	AV1921E324R04	6-2213767-8	
SILVER	RED	24V	AV1921E324Q04	6-2213767-7	
GOLD	RED	12V	AV1921E312R04	6-2213767-6	
SILVER	RED	12V	AV1921E312Q04	6-2213767-5	
GOLD	WHITE	24V	AV1921E124R04	6-2213767-4	
SILVER	WHITE	24V	AV1921E124Q04	6-2213767-3	
GOLD	WHITE	12V	AV1921E112R04	6-2213767-2	
SILVER	WHITE	12V	AV1921E112Q04	6-2213767-1	
GOLD	BLUE	24V	AV1920E724R04	6-2213767-0	
SILVER	BLUE	24V	AV1920E724Q04	5-2213767-9	
GOLD	BLUE	12V	AV1920E712R04	5-2213767-8	
SILVER	BLUE	12V	AV1920E712Q04	5-2213767-7	
GOLD	GREEN	24V	AV1920E624R04	5-2213767-6	
SILVER	GREEN	24V	AV1920E624Q04	5-2213767-5	
GOLD	GREEN	12V	AV1920E612R04	5-2213767-4	
SILVER	GREEN	12V	AV1920E612Q04	5-2213767-3	
GOLD	YELLOW	24V	AV1920E524R04	5-2213767-2	
SILVER	YELLOW	24V	AV1920E524Q04	5-2213767-1	
GOLD	YELLOW	12V	AV1920E512R04	5-2213767-0	
SILVER	YELLOW	12V	AV1920E512Q04	4-2213767-9	
GOLD	RED	24V	AV1920E324R04	4-2213767-8	
SILVER	RED	24V	AV1920E324Q04	4-2213767-7	
GOLD	RED	12V	AV1920E312R04	4-2213767-6	
SILVER	RED	12V	AV1920E312Q04	4-2213767-5	
GOLD	WHITE	24V	AV1920E124R04	4-2213767-4	
SILVER	WHITE	24V	AV1920E124Q04	4-2213767-3	
GOLD	WHITE	12V	AV1920E112R04	4-2213767-2	
SILVER	WHITE	12V	AV1920E112Q04	4-2213767-1	
POLE/THROW	CONTACT	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PN	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

-

DWN 08FEB2016
NAGALAKSHMI K

CHK 08FEB2016
HILL RYAN

APVD 08FEB2016
HILL RYAN

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

ANTI-VANDAL SWITCH 19mm
MOVING RING LED

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2213767

-

SCALE 1:1

SHEET 4 OF 4

REV B1

1471-9 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2213767-8](#)