

## REVISIONS

| P | LTR | DESCRIPTION      | DATE      | DWN | APVD |
|---|-----|------------------|-----------|-----|------|
|   | J   | PRODUCTION ISSUE | 28JAN2019 | PNT | MT   |





TABLE OF DIMENSIONS

| PART NUMBER | H              |                | J                     |                      |              | P               | R             | S             | T              | U             | JO             | HW            | JW             |
|-------------|----------------|----------------|-----------------------|----------------------|--------------|-----------------|---------------|---------------|----------------|---------------|----------------|---------------|----------------|
|             | Min<br>a       | Max<br>b       | Min<br>-3,-4,-25<br>a | Min<br>-12,-100<br>a | Max<br>b     | ±10%<br>b       | Ref<br>b      | Ref<br>b      | Ref<br>b       | ±10%<br>b     | ±10%<br>b      | ±20%<br>b     | ±20%<br>b      |
| 222D921     | 19.3<br>[.76]  | 13.0<br>[.51]  | 6.3<br>[.25]          | 4.5<br>[.18]         | 2.1<br>[.08] | 44.5<br>[1.75]  | 16.3<br>[.64] | 3.05<br>[.12] | 1.02<br>[.04]  | 5.6<br>[.22]  | 21.8<br>[.86]  | 1.52<br>[.06] | 1.14<br>[.045] |
| 222D932     | 26.1<br>[1.03] | 19.1<br>[.75]  | 7.6<br>[.30]          | 5.6<br>[.22]         | 2.6<br>[.10] | 67.3<br>[2.65]  | 18.0<br>[.71] | 3.05<br>[.12] | 1.02<br>[.04]  | 8.4<br>[.33]  | 29.2<br>[1.15] | 1.78<br>[.07] | 1.14<br>[.045] |
| 222D953     | 34.2<br>[1.35] | 26.0<br>[1.02] | 9.6<br>[.38]          | 6.6<br>[.26]         | 3.0<br>[.12] | 81.3<br>[3.20]  | 18.8<br>[.74] | 3.05<br>[.12] | 1.02<br>[.04]  | 11.4<br>[.45] | 36.3<br>[1.39] | 1.78<br>[.07] | 1.14<br>[.045] |
| 222D963     | 43.6<br>[1.72] | 34.1<br>[1.34] | 11.4<br>[.45]         | 7.8<br>[.31]         | 3.6<br>[.14] | 115.6<br>[4.55] | 21.3<br>[.84] | 3.05<br>[.12] | 1.65<br>[.065] | 15.5<br>[.61] | 47.0<br>[1.85] | 1.78<br>[.07] | 1.14<br>[.045] |

DIMENSIONS:

mm [INCHES]

DWN

PRAVEEN N T

28JAN2019

MATERIAL

SEE SHEET 2

FINISH

-

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

CHK

N NAGAR

28JAN2019

APVD

M TAYLOR

28JAN2019

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

NAME

BOOT, 90 DEGREE,  
WITH LIP

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-

222D921-XX-0THRU963-XX-0

RESTRICTED TO

-

CUSTOMER DRAWING


SCALE

DNS

SHEET

1 OF 2

REV J



THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

0 PLC ± -  
 1 PLC ± -  
 2 PLC ± -  
 3 PLC ± -  
 4 PLC ± -  
 ANGLES ± -

| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|           | —   | SEE SHEET 1 | —    | —   | —    |

| COMPATABILITY CHART |                                   |         |                   |                   |
|---------------------|-----------------------------------|---------|-------------------|-------------------|
| MATERIAL DASH NO.   | MATERIAL DESCRIPTION              | RT SPEC | COATING SLASH NO. | COATING S NO.     |
| -3                  | Polyolefin, Semi-rigid            | RT-301  | /42;/86;/180      | S1017;S1048;S1030 |
| -4                  | Polyolefin, Flexible              | RT-1304 | /42;/86;/180      | S1017;S1048;S1030 |
| -12                 | Fluoroelastomer, Flexible         | RT-1312 | N/A               | N/A               |
| -25                 | Elastomer, Fluid Resistant        | RW-2070 | /42;/86;/225      | S1017;S1048;S1206 |
| -100                | Polyolefin, Semi-flexible ZEROHAL | RW-2082 | /86;/180          | S1048;S1030       |

ORDERING INFORMATION

222D9XX-XX-XX/XX-0

Base part number

Material dash number  
(See Compatability Chart)

Modification number

Adhesive slash number  
(If necessary, see Compatability Chart)

Color designator

NOTES


1. Dimensions appearing in table are as follows:  
a - As Supplied  
b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - TE Connectivity Ltd.

|                                                                                     |  |                  |           |                                                                                                                      |           |            |                          |
|-------------------------------------------------------------------------------------|--|------------------|-----------|----------------------------------------------------------------------------------------------------------------------|-----------|------------|--------------------------|
| DIMENSIONS:                                                                         |  | DWN              | 28JAN2019 | MATERIAL                                                                                                             |           | FINISH     |                          |
| mm [INCHES]                                                                         |  | PRAVEEN N T      |           | -                                                                                                                    |           |            |                          |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                              |  | CHK              | 28JAN2019 | <div></div> TE Connectivity Ltd. |           |            |                          |
|                                                                                     |  | N NAGAR          |           |                                                                                                                      |           |            |                          |
|                                                                                     |  | APVD             | 28JAN2019 | M TAYLOR                                                                                                             |           |            |                          |
|                                                                                     |  | PRODUCT SPEC     |           | NAME                                                                                                                 |           |            |                          |
|                                                                                     |  | -                |           | BOOT, 90 DEGREE,<br>WITH LIP                                                                                         |           |            |                          |
| 0 PLC ± -                                                                           |  | APPLICATION SPEC |           | SIZE                                                                                                                 | CAGE CODE | DRAWING NO | RESTRICTED TO            |
| 1 PLC ± -                                                                           |  | -                |           | A4 00779 C-                                                                                                          |           |            | 222D921-XX-0THRU963-XX-0 |
| 2 PLC ± -                                                                           |  | APPLICATION SPEC |           |                                                                                                                      |           |            |                          |
| 3 PLC ± -                                                                           |  | -                |           |                                                                                                                      |           |            |                          |
| 4 PLC ± -                                                                           |  | WEIGHT           |           |                                                                                                                      |           |            |                          |
| ANGLES ± -                                                                          |  |                  |           |                                                                                                                      |           |            |                          |
|  |  | CUSTOMER DRAWING |           |                                                                                                                      | SCALE     | DNS        | SHEET 2 OF 2             |
|                                                                                     |  |                  |           |                                                                                                                      | REV J     |            |                          |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[222D953-3/42-0](#)