








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	PRELIMINARY	11OCT2014	DLD	CJS
	A	RELEASED PER ECO-15-002891	24FEB2015	DLD	CJS
	A1	REVISED PER ECO-18-013523	28AUG2018	JMS	CS
	A2	REVISED PER ECO-19-004164	25MAR2019	JMS	CS

- ⚠ TPA SHIPPED IN PRE-LATCHED POSITION.
2. 2288274-1 SHOWN IN GENERAL VIEWS.
- ⚠ THIS PART NUMBER HAS NOT COMPLETED VALIDATION TESTING.
- ⚠ PRELIMINARY - NOT RELEASED FOR PRODUCTION
- ⚠ DUE TO BULK PACKAGED ARRANGEMENT, TPA MAY BE MOVED FROM THE PRE-LATCHED POSITION TO CLOSED OR PARTIALLY CLOSED DURING SHIPMENT. PLEASE REFER TO TE SPECIFICATION 408-32044 FOR TPA RESET INSTRUCTIONS.
6. APPLICABLE RECEPTACLES FOR THIS CONNECTOR:  
0.64 GENERATION Y - TE P/N'S 2035334-X AND 1924955-X
- 2.8 CIRCUITS - FCI APEX 2.8 FAMILY, REF P/N 54001431 OR SIMILAR (ACCEPTS 10AWG - 22AWG)



⚠	D	---	2288274-4
	C	BROWN	2288274-3
	B	GRAY	2288274-2
	A	BLACK	2288274-1
	KEYING OPTION	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. DRUMMOND	17OCT2014	 TE Connectivity	
		CHK C. SCHMID	17OCT2014		
		APVD C. SCHMID	17OCT2014	NAME  PLUG ASSEMBLY, 24 POSITION UNSEALED HYBRID (4X 2.8, 20X 0.64)	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.3 3 PLC ± 4 PLC ± ANGLES ±°		CAGE CODE	
				DRAWING NO	
MATERIAL		FINISH		RESTRICTED TO	
-		-		A100779C2288274	
		Customer Drawing		SCALE 4:1	
				SHEET 1 OF 1	
				REV A2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2288274-2](#)