




- NOTES
Bemerkungen
- 1



WEIGHT WITHOUT CARRIER STRIP
Gewicht ohne Trägerstreifen
- 2

CONTACT KIT PART NUMBER FOR REFERENCE ONLY
COMPONENTS MUST BE PURCHASED SEPARATELY
Kontaktkit Teilenummer nur zur Referenz
Komponenten sind einzeln zu bestellen
- 3

ALLOWED AREA FOR CONTACT GRIPPING
FOR CABLE TERMINATION
Zulaessiger Bereich zum Greifen des
Kontaktes bei der Kabelverarbeitung
- 4

DURING THE PROCCESING, THE CONTACT
MAY BE LOADED WITH MAX. 35N IN AXIAL DIRECTION
Bei der Verarbeitung darf der Kontakt an
gezeigter Stelle axial mit max. 35N belastet werden
- 5

ALTERNATIVE 2298126-2 (=2298126-1 IN OPPOSITE REELING DIRECTION)
Alternativ 2298126-2 (=2298126-1 in entgegengesetzter Wickelrichtung)



2298490-1	1	2298126-1	C	FERRULE,RTK031 Stuetzhulse,RTK031		STAINLESS STEEL	PLAIN Blank	0.035	3
	1	2298125-1	A	PIN CENTER CONTACT,RTK031 Innenleiter Stiftkontakt,RTK031		CuSn	Ag	0.026	2
	1	2298123-1	A	SUBASSEMBLY, RTK031 PIN CONTACT	PIN Outer Contact	CuSn	Sn	0.54	1
CONTACTKIT PART NUMBER		PIECE Stueck	PART No		Dielectric	PBT	Green RAL 6018 Similar		
		REV		DESCRIPTION Benennung		MATERIAL Werkstoff	SURFACE Oberflaeche	WEIGHT (g)	ITEM Pos.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Weinberger 03APR2017	TE Connectivity			
DIMENSIONS: mm		CHK S.Aboukassem 16MAY2017				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C.Schrettlinger 28JUN2017	NAME MATE-AX 180DEG PIN CONTACT, ASSY MATE-AX 180Grad Stiftkontakt, Assy CABLE RTK031		
	0 PLC ±0.2 1 PLC ±0.1 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC 108-94515 APPLICATION SPEC 114-94413	SIZE A2	CAGE CODE 00779	DRAWING NO C=2298490
MATERIAL -		FINISH -	WEIGHT -	RESTRICTED TO -		
			CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 2	REV A2

4

3




2

1


THIS DRAWING IS UNPUBLISHED	RELEASED FOR PUBLICATION
 COPYRIGHT 2017	BY TE Connectivity Germany GmbH
ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SECTION A-A



5:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Weinberger CHK S.Aboulkassem APVD C.Schrettlinger		03APR2017 16MAY2017 28JUN2017		 TE Connectivity							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		MATE-AX 180DEG PIN CONTACT, ASSY MATE-AX 180Grad Stiftkontakt, Assy CABLE RTK031							
mm		0 PLC ±0.2 1 PLC ±0.1 2 PLC ±0.1 3 PLC ±- 4 PLC ±- ANGLES ±1°		PRODUCT SPEC 108-94515 APPLICATION SPEC 114-94413		SIZE A2		CAGE CODE 00779		DRAWING NO C=2298490		RESTRICTED TO -	
MATERIAL		FINISH		WEIGHT -		CUSTOMER DRAWING		SCALE 5:1		SHEET 2 OF 2		REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2298123-1](#)