


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	07AUG2017	C.W	I.Y
	B	REVISED PER PCN E-19-014633	15FEB2019	AK	NS




NOTES:

1. SECONDARY WEDGE LOCK SOLD SEPARATELY: W2PX-XXXX.
(X = A,B,C,D KEY, XXXX = ALL MODIFICATIONS)
2. THIS RECEPTACLE MATES WITH DT06-2S-XXXX PLUG.
(XXXX = ALL MODIFICATIONS)
3. MATERIAL: HOUSING: PA66 GF15, SEE TABLE FOR COLOR
GROMMET: VMQ SEE TABLE FOR COLOR
4. DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS. (17 = 2017)
MONTH:THIRD DIGIT, EXCLUDING I. A = JAN, B = FEB,
C = MARCH ... (K = OCTOBER)
DAY: FOURTH AND FIFTH DIGITS (14 = 14th DAY)
HOUR:SIXTH AND SEVENTH DIGITS (11 = 11AM)
5. "E" IDENTIFIES E-SEAL.
6. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS SEE CUSTOMER DRAWING 0425-015-0000.
7. XXXX IDENTIFIES THE MODIFICATION NUMBER,
IF APPLICABLE. EXAMPLE: "TB31" FOR DT04-2P-TB31,


CONTACT SIZE	WIRE RANGE	SEALING RANGE	SEAL IDENTIFICATION
#16	14-20AWG (2.5-0.5mm ²)	.088-.145 [2.23-3.68]	STANDARD SEAL N-SEAL
		.053-.120 [1.35-3.05]	EXTRA THIN SEAL E-SEAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. WAN	15OCT2017		 TE Connectivity	
DIMENSIONS: mm		CHK E. JIANG	15OCT2017		DT SERIES, SNAP CAPS 2 WAY RECEPTACLE, DT04-2P-TXXX	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L. YIN	15OCT2017			
		PRODUCT SPEC 108-151009		SIZE CAGE CODE DRAWING NO		
0 PLC ±. 1 PLC ±. 2 PLC ±0.64 3 PLC ±0.64 4 PLC ±. ANGLES ±. FINISH		APPLICATION SPEC 114-151009				
MATERIAL 		WEIGHT SEE TABLES		A200779		C-2303812
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 2	REV B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



5		5					
		1	1	GREY	PA66-GF15	STD CAP	3
1	1			BLACK	PA66-GF15	STD CAP	
1			1	BURNT RED	VMQ	GROMMET,E-SEAL	2
	1	1		ORANGE-RED	VMQ	GROMMET,N-SEAL	
		1	1	GREY	PA66-GF15	HOUSING	1
1	1			BLACK	PA66-GF15	HOUSING	
				COLOUR	MATERIAL	DESCRIPTION	ITEM NO
4.46	4.46	4.46	4.46	WEIGHT OF EACH ASSY NO. (g)			
B	A	A	B	REVISION OF EACH ASSY NO.			
DT04-2P -TE32	DT04-2P -TN32	DT04-2P -TN31	DT04-2P -TE31	DEUTSCH PN			
1--4	1--3	1--2	1--1	TE PN			
DT04-2P -CE03	DT04-2P -E005	DT04-2P -E003 -FP04	DT04-2P -CE01	COMPARABLE PART			



5		5					
		1	1	GREY	PA66-GF15	LONG CAP	3
1	1			BLACK	PA66-GF15	LONG CAP	
1			1	BURNT RED	VMQ	GROMMET,E-SEAL	2
	1	1		ORANGE	VMQ	GROMMET,N-SEAL	
		1	1	GREY	PA66-GF15	HOUSING	1
1	1			BLACK	PA66-GF15	HOUSING	
QTY. REQUEST PER ASSY				COLOR	MATERIAL	DESCRIPTION	ITEM NO
6.52	6.52	6.52	6.52	WEIGHT OF EACH ASSY NO. (g)			
B	A	A	B	REVISION OF EACH ASSY NO.			
DT04-2P -TE82	DT04-2P -TN82	DT04-2P -TN81	DT04-2P -TE81	DEUTSCH PN			
2--4	2--3	2--2	2--1	TE PN			
DT04-2P -CE09	DT04-2P -FE01	DT04-2P -FE08	DT04-2P -CE04	COMPARABLE PART			

THIS DRAWING IS A CONTROLLED DOCUMENT.		C.WAN 15OCT2017 CHK 15OCT2017 E. JIANG 15OCT2017 APVD 15OCT2017 L. YIN PRODUCT SPEC 108-151009 APPLICATION SPEC 114-151009		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.64 3 PLC ±0.64 4 PLC ±- ANGLES ±- FINISH -		NAME DT SERIES, SNAP CAPS 2 WAY RECEPTACLE, DT04-2P-TXXX	
MATERIAL 		WEIGHT SEE TABLES		SIZE CAGE CODE DRAWING NO RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 3:1	
SHEET 2 OF 2				REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2303812-1](#)