

NOTES:

MATERIAL:
HOUSING: LCP, UL94 VO, BLACK
CONTACT: PHOSPHOR BRONZE, 0.20mm THICK,

ALL OVER 3-5 μ m TIN OVER MIN 1.27 μ m NICKEL UNDERPLATE


CONTACT AREA: MIN 0.1 μ m GOLD
SOLDER TAIL: 3-5 μ m TIN
UNDERPLATING: MIN 1.27 μ m NICKEL ALL OVER

CONTACT AREA: MIN 0.38 μ m GOLD
SOLDER TAIL: 3-5 μ m TIN
UNDERPLATING: MIN 1.27 μ m NICKEL ALL OVER

CONTACT AREA: MIN 0.76 μ m GOLD
SOLDER TAIL: 3-5 μ m TIN
UNDERPLATING: MIN 1.27 μ m NICKEL ALL OVER

N = NO. OF POSITIONS PER CONNECTOR.

5:1



2- -8

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28NOV2017 SOURAV DAS CHK 22NOV2018 SHARATH S APVD 22NOV2018 PRASHANTH S PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32186		 TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		NAME AMPMODU 2mm, BtB RECEPTACLE, DUAL ROW HORIZONTAL, TH/THR -							
				SIZE A2		CAGE CODE 00779		DRAWING NO C=2307712		RESTRICTED TO -	
MATERIAL 		SEE NOTES -		WEIGHT -		CUSTOMER DRAWING					
						SCALE 5:1		SHEET 1 of 2		REV A2	

4

3

2

I

© 2021 TE Connectivity. All Rights Reserved.

MATING SIDE PLATING (FINISH)	“L”SOLDER TAIL LENGTH	BTB RECEPTACLE BASE NUMBERS	
		TAPE & REEL PKG W/O CAP	TUBE PKG W/O CAP
TIN △ 2	2.1	2307712	2314915
	2.8	2314923	2307713
	3.4	A/R	2307714
GOLD FLASH 0.1µm △ 3	2.1	2307715	2314916
	2.8	2314924	2307716
	3.4	A/R	2307717
GOLD 0.38µm △ 4	2.1	2307718	2314917
	2.8	2314925	2307719
	3.4	A/R	2307720
GOLD 0.76µm △ 5	2.1	2307721	2314918
	2.8	2314926	2307722
	3.4	A/R	2307723

* A/R- AVAILABLE ON REQUEST

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

48	50	50	5- -0
46	48	48	4- -8
44	46	46	4- -6
42	44	44	4- -4
40	42	42	4- -2
38	40	40	4- -0
36	38	38	3- -8
34	36	36	3- -6
32	34	34	3- -4
30	32	32	3- -2
28	30	30	3- -0
26	28	28	2- -8
24	26	26	2- -6
22	24	24	2- -4
20	22	22	2- -2
18	20	20	2- -0
16	18	18	1- -8
14	16	16	1- -6
12	14	14	1- -4
10	12	12	1- -2
8	10	10	1- -0
6	8	8	-8
4	6	6	-6
2	4	4	-4
DIM “F”	DIM “E”	N/6	FG PN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±0.1
3 PLC ±
4 PLC ±
ANGLES ±°
FINISH

SEE NOTES
-

DWN 28NOV2017
CHK SOURAV DAS
SHARATH S
APVD 22NOV2018
PRASHANTH S

PRODUCT SPEC
108-64040

APPLICATION SPEC
114-32186

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
AMPMODU 2mm, BtB RECEPTACLE,
DUAL ROW HORIZONTAL, TH/THR
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2307712

RESTRICTED TO
-

SCALE
5:1

SHEET
2

OF
2

REV
A2

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2314924-8](#)