


P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL ISSUE	19AUG2020	SM	MZ
	2	DRAFTING UPDATES	03SEP2020	SM	MZ
	A	PRODUCT UNDER TESTING	24NOV2020	SM	MZ

NOTES:

- MATERIALS:
PLASTICS: PBT+PC ALLOY, UL-V0, UV-F1
CONTACTS: COPPER ALLOY, TIN PLATED
- OPERATING RATINGS :
VOLTAGE (max): 600Vac Max
CURRENT (max): 25A ON 4.0mm² & 20A ON 12AWG
TEMPERATURE : -40°C TO 85°C
IP RATING : IP67 & IP68
- FOR ASSEMBLY INSTRUCTIONS, REFER APPLICATION SPECIFICATION 114-133123
- PACKAGING: MOQ 200 pcs IN PE BAG




SCALE 1:1



PRODUCT UNDER TESTING

CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT


KEY B	MULTI SPLITTER	2359421-2
KEY A		2359421-1
POLARIZING KEY	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH.M 19AUG2020	 TE Connectivity		
		CHK M. ZUCCA 03SEP2020			
		APVD PETER OTT 24NOV2020	NAME NECTOR T, 3Pos, MULTI SPLITTER		
		PRODUCT SPEC 108-133123			
		APPLICATION SPEC 114-133123			
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2359421
		CUSTOMER DRAWING	SCALE 3:2	SHEET 1 OF 1	REV A

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC ±0.4	
		1 PLC ±0.4	
		2 PLC ±0.1	
		3 PLC ±	
		4 PLC ±	
		ANGLES ±1°	
MATERIAL -		FINISH -	
		-	



POLARIZING KEY A
2359421-1



POLARIZING KEY B
2359421-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2359421-1](#) [2359421-2](#)