








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	13JUL2021	J.J	N.S




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	26SEP2019	 TE Connectivity Ltd.		
		H.X				
		CHK	26SEP2019	NAME		
		W.H				
		APVD	-	0.4mm PITCH BTB CONN. H0.8 REC ASSEMBLY		
		PRODUCT SPEC				
		108-115166		SIZE		
		APPLICATION SPEC				
		WEIGHT	-	A2 00779		
		CUSTOMER DRAWING				
		SCALE	12:1	SHEET 1 of 6		
		REV	A			



NOTES:
1.MATERIAL:
1.1 HOUSING: LCP, UL 94 V-0, COLOR: BLACK.
1.2 CONTACT: COPPER ALLOY.
1.3 HOLD DOWN: COPPER ALLOY.
2. FINISH:
2.1 CONTACT:
GOLD FLASH ON CONTACT AND SOLDERING AREA.
NICKEL UNDER PLATING OVERALL.
2.2 HOLD DOWN:
TIN PLATING OVER NICKELUNDER PALTING.
3.REFLOW SOLDER CAPABLE TO 260 °C.
4.MATING PLUG PART NUMBER:3-2363962-0.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	26SEP2019	<div>TE</div> TE Connectivity Ltd.			
		H.X	26SEP2019				
		CHK	W.H	NAME			
		APVD	-	PRODUCT SPEC			
				108-115166			
				APPLICATION SPEC			
				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A2	00779	C=2363961	-
				CUSTOMER DRAWING		SCALE	12:1
				SHEET		2 of 6	REV
						A	








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

C

B

A






D

C


B


A

2363961


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN H.X 26SEP2019		<div></div> TE Connectivity Ltd.															
				CHK W.H 26SEP2019																	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD —	—	NAME 0.4mm PITCH BTB CONN. H0.8 REC ASSEMBLY —															
		0 PLC ± —		PRODUCT SPEC																	
		1 PLC ± 0.3		108-115166																	
		2 PLC ± 0.20		APPLICATION SPEC																	
		3 PLC ± 0.15		—																	
		4 PLC ± —		—																	
		ANGLES ± ±		—																	
MATERIAL —		FINISH —		WEIGHT 0		A2		00779		C=2363961		RESTRICTED TO —									
				CUSTOMER DRAWING						SCALE		12:1		SHEET		4 of 6		REV		A	

4-2363961-0
PART NUMBER

 TE		TE Connectivity Ltd.	
NAME			
0.4mm PITCH BTB CONN.			
H0.8 REC ASSEMBLY			
—			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2363961	—
		SCALE 12:1	SHEET 5 of 6
			REV A



MATING HIGHT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.X	26SEP2019
DIMENSIONS: mm		CHK W.H	26SEP2019
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD —	—
	0 PLC ±	PRODUCT SPEC	
	1 PLC ± 0.3	108-115166	
	2 PLC ± 0.20	APPLICATION SPEC	
	3 PLC ±	—	
	4 PLC ±	—	
ANGLES ± ±		—	
MATERIAL —	FINISH —	WEIGHT —	
		CUSTOMER DRAWING	

2363961

C

- B

51



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2363961-0](#)