










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	13JUL2021	J.J	N.S




3-2363962-0  
PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.X	26SEP2019	 TE Connectivity Ltd.	
		CHK W.H	26SEP2019		
		APVD —	—	NAME	
		PRODUCT SPEC 108-115166		0.4mm PITCH BTB CONN. H0.8 PLUG ASSEMBLY	
		APPLICATION SPEC —		—	
MATERIAL 		WEIGHT —		SIZE A2	RESTRICTED TO —
FINISH 		CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO C-2363962
		SCALE 16:1		SHEET 1 of 6	REV A





NOTES:  
1.MATERIAL:  
1.1 HOUSING: LCP, UL 94 V-0, COLOR: BLACK.  
1.2 CONTACT: COPPER ALLOY.  
1.3 HOLD DOWN: COPPER ALLOY.  
  
2. FINISH:  
2.1 CONTACT:  
GOLD FLASH ON CONTACT AND SOLDERING AREA.  
NICKEL UNDER PLATING OVERALL.  
2.2 HOLD DOWN:  
GOLD FLASH PLATING OVER NICKELUNDER PALTING.  
  
3.REFLOW SOLDER CAPABLE TO 260 °C.  
4.MATING PLUG PART NUMBER: 3-2363961-0.

2363962






9.0KG	0.98KG	5000	14	70000	3-2363962-0
GROSS WEIGHT	NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	PART NUMBER





OUT BOX PACKAGE DIAGRAM DRAWING


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.X CHK W.H 26SEP2019		 TE Connectivity Ltd.			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± -		0.4mm PITCH BTB CONN. H0.8 PLUG ASSEMBLY -			
		1 PLC ± 0.3					
		2 PLC ± 0.20					
3 PLC ± -		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
4 PLC ± -		108-115166					
ANGLES ± -		APPLICATION SPEC					
MATERIAL		FINISH		WEIGHT		A2 00779 C=2363962	
-		-		-		-	
CUSTOMER DRAWING				SCALE		SHEET	
				16:1		3 OF 6	
						REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-






4-2363962-0  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.X 26SEP2019		 TE Connectivity Ltd.		
		CHK W.H 26SEP2019				
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME  0.4mm PITCH BTB CONN. H0.8 PLUG ASSEMBLY  —		
		APVD —				
		PRODUCT SPEC 108-115166				
MATERIAL  —		APPLICATION SPEC —		SIZE		
		WEIGHT —		CAGE CODE		
		CUSTOMER DRAWING		DRAWING NO		
				RESTRICTED TO		
				A2 00779 C=2363962		
				—		
				SCALE		
				16:1		
				SHEET		
				4 of 6		
				REV		
				A		



NOTES:  
1.MATERIAL:  
1.1 HOUSING: LCP, UL 94 V-0, COLOR: BLACK.  
1.2 CONTACT: COPPER ALLOY.  
1.3 HOLD DOWN: COPPER ALLOY.  
2. FINISH:  
2.1 CONTACT:  
GOLD FLASH ON CONTACT AND SOLDERING AREA.  
NICKEL UNDER PLATING OVERALL.  
2.2 HOLD DOWN:  
GOLD FLASH PLATING OVER NICKELUNDER PALTING.  
3.REFLOW SOLDER CAPABLE TO 260 °C.  
4.MATING PLUG PART NUMBER: 4-2363961-0.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.X 26SEP2019		<div>TE Connectivity Ltd.</div>			
		CHK W.H 26SEP2019					
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME  0.4mm PITCH BTB CONN. H0.8 PLUG ASSEMBLY  —			
		APVD —					
		PRODUCT SPEC 108-115166					
		APPLICATION SPEC —					
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C-2363962	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 16:1	SHEET 5 of 6	REV A	



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2363962-0](#)