






| P | LTR | DESCRIPTION        | DATE       | DWN | APVD |
|---|-----|--------------------|------------|-----|------|
|   | A   | PRODUCTION RELEASE | 24 JAN2022 | SCB | PS   |
|   |     |                    |            |     |      |
|   |     |                    |            |     |      |



2385008-3 AS SHOWN



NOTES:


1 MATERIALS & FINISH  
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN  
CONTACT : BRASS, TIN PLATED

3. ELECTRICAL  
RATED CURRENT AND VOLTAGE : 16AMP 300V(UG B)  
: 10AMP 300V(UG D)  
INSULATION RESISTANCE : >2000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

4 TOLERANCE NOT CUMULATIVE

|       |             |             |
|-------|-------------|-------------|
| 82.88 | 16          | 1-2385008-6 |
| 77.80 | 15          | 1-2385008-5 |
| 72.72 | 14          | 1-2385008-4 |
| 67.64 | 13          | 1-2385008-3 |
| 62.56 | 12          | 1-2385008-2 |
| 57.48 | 11          | 1-2385008-1 |
| 52.40 | 10          | 1-2385008-0 |
| 47.32 | 9           | 2385008-9   |
| 42.24 | 8           | 2385008-8   |
| 37.16 | 7           | 2385008-7   |
| 32.08 | 6           | 2385008-6   |
| 27.00 | 5           | 2385008-5   |
| 21.92 | 4           | 2385008-4   |
| 16.84 | 3           | 2385008-3   |
| 11.76 | 2           | 2385008-2   |
| DIM A | NO. OF POS. | TE PN       |

|                                                                                                           |  |                                 |                                                                                                       |                    |                         |
|-----------------------------------------------------------------------------------------------------------|--|---------------------------------|-------------------------------------------------------------------------------------------------------|--------------------|-------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                    |  | DWN 24 JAN2022<br>SHRICHARANA B |  TE Connectivity |                    |                         |
| DIMENSIONS:<br>mm                                                                                         |  | CHK 24 JAN2022<br>SUBHASREE S   |                                                                                                       |                    |                         |
|                      |  | APVD 24 JAN2022<br>PRASHANTH S  |                                                                                                       |                    |                         |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ± |  | PRODUCT SPEC<br>108-32299       |                                                                                                       |                    |                         |
| MATERIAL 1                                                                                                |  | APPLICATION SPEC<br>114-32242   | NAME<br>TERMINAL BLOCK, 90 DEG HEADER,<br>PITCH 5.08mm, TAIL LENGTH 4.5mm                             |                    |                         |
| FINISH 1                                                                                                  |  | WEIGHT<br>-                     | SIZE<br>A3                                                                                            | CAGE CODE<br>00779 | DRAWING NO<br>C-2385008 |
| CUSTOMER DRAWING                                                                                          |  |                                 | RESTRICTED TO<br>-                                                                                    | SCALE<br>4:1       | SHEET<br>1 OF 1         |
|                                                                                                           |  |                                 |                                                                                                       | REV<br>A           |                         |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2385008-8](#)